


# MILITARY DEVICES

## SPIDER® II




# Built to Military Requirements!



### Spider II

Introducing Spider II power distribution products customized for use in Military applications. These new products are built to military requirements and are presently deployed domestically and abroad. All units feature Straight Blade or Twist-lock® watertight receptacles, individual GFCI modules, electronic supervisory circuit and are completely field serviceable.



### Ordering Information

Rating	Type	Qty	Receptacle Ratings	Receptacle Components	Protection Overload	GFI	Catalog Number
60A, 3Ø 120/208V AC (max.)	Straight Blade	6	20A, 125V	HBL53R61	Yes	Yes*	<b>SCSB0M2</b>
	Class "L" (inlet)	1	60A, 3ØY, 120/208V	—	No	No	
	Class "L" (outlet)	1	60A, 3ØY, 120/208V	—	No	No	
60A, 3Ø 120/208V AC (max.)	Twist-Lock®	6	20A, 125V	HBL2310SW	Yes	Yes*	<b>SCTLOM2</b>
	Class "L" (inlet)	1	60A, 3ØY, 120/208V	—	No	No	
	Class "L" (outlet)	1	60A, 3ØY, 120/208V	—	No	No	

\* GFCI protection on 4 devices only

### Specifications

Operation Indoor & Outdoor Wet and Dry Locations  
 Enclosure Type 3R, Rainproof, Suitable for use in damp locations



Wiring Device-Kellems

[www.hubbell-wiring.com](http://www.hubbell-wiring.com)

# Safe, Reliable Innovative!

### **NEW! 30 Amp Spider II**

Now available, the 30 Amp version of the industry standard power distribution box. Incorporating all the standard features of the standard box including GFCI and overload protection and Watertight Shrouded Receptacles.

These units feature the new Reverse Service Watertight Shrouded inlet and a 30A Hubbell Twist-Lock® receptacle for downstream power.



### Ordering Information

Rating	Type	Qty	Receptacle Ratings	Receptacle Components	Protection Overload	GFI	Catalog Number
30A, 120/240V AC (max.)	Straight Blade	6	20A, 125V	HBL53R61	Yes	Yes	<b>SDSB1</b>
	Twist-Lock®	1	30A, 250V	HBL2620SW	Yes	No	
	Twist-Lock® (Inlet)	1	30A, 120/240V	HBL2715SWR	No	No	
	Twist-Lock® (outlet)	1	30A, 120/240V	HBL2710	No	No	

30A Reverse Service Safety-Shroud Connector (sold separately): **HBL2713SR**

Spider II replacement parts available. Contact Hubbell for availability.

### Specifications

Listings/Certifications	UL1640, UL943
Operation	Indoor & Outdoor Wet and Dry Locations
Enclosure Type	3R, Rainproof, Suitable for use in damp locations
Code Compliance	NEC, ANSI/NFPA70

