

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19154-0022](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Step Down Butt Splice for 14-22 AWG Wire Blue w/Red Stripe

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Splices  
 Series [19154](#)  
 Comments Step down: 14/16 to 18/22 AWG . Blue with Red Stripe  
 Crimp Quality Equipment Yes  
 Mil-Spec N/A  
 MolexKits Yes  
 Overview [Splices](#)  
 Product Name Butt - Step Down  
 UPC 800753108875

**Physical**

Barrel Type Closed - Brazed  
 Color - Resin Blue  
 Flammability 94V-0  
 Insulation PVC  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Material - Plating Termination Tin  
 Material - Resin PVC  
 Net Weight 1.730/g  
 Packaging Type Bag  
 Temperature Range - Operating -40°C to +105°C  
 Wire Insulation Diameter 4.45mm max.  
 Wire Size AWG 14, 16, 18, 20, 22

**Electrical**


Voltage - Maximum 600V

**Material Info**

Old Part Number BA-631X

**Reference - Drawing Numbers**

Product Specification PS-19902-011, PS-19902-013  
 Sales Drawing SD-19154-007



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

[19154Series](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are  
found by selecting the products below.  
Crimp Height Specifications are then  
contained in the Application Tooling  
Specification document.*

**Global**

Description	Product #
Crimp Head for the AT-200™ Pneumatic Hand Tool	<a href="#">0640050100</a>
PremiumGrade™ Hand Crimp Tool	<a href="#">0640010100</a>