

5

4

3

2

1

DRAWING NO.
32-1414-CUST(SEE TABLE I)

REVISIONS

| | | | | | |
|----|------------------|---|---|---|--|
| 01 | OFFICIAL RELEASE | | | | 2009.09.01 8091802 Betty +08000 |
| | 08-05-09 | Y | U | T | |



Description: See Table I
 Part No: See Table I
 Application: Flat Silver Satin Cable Assembly
 Crimp Tool: N/A
 Impedance: N/A
 Frequency Range: N/A
 Material: Cable Gray
 RJ11 6P4C
 RoHS Compliance: Yes
 Technical Detail: N/A

| 受控 CONTROLLED DOCUMENT | | | | | |
|------------------------|--------------|-----------|----|------------------|-----------|
| 编号 P/N | 30-14XX-CUST | 版本 Rev | 01 | 日期 Rel'd Date | SEP 14,09 |





TABLE I

| P/N | Description | Color | Length |
|---------|------------------------------|-------|--------|
| 32-1414 | FLAT 6P4C,VOICE,S SATIN,7FT | Gray | 7FT |
| 32-1434 | FLAT 6P4C,VOICE,S SATIN,15FT | Gray | 15FT |
| 32-1454 | FLAT 6P4C,VOICE,S SATIN,25FT | Gray | 25FT |

CUSTOMER COPY



PIN ASSIGNMENT

| | |
|-----|----------|
| P 1 | P 2 |
| 2 | 5 YELLOW |
| 3 | 4 GREEN |
| 4 | 3 RED |
| 5 | 2 BLACK |

DIM OUTLINE

| | | | |
|--------------------------------------|--------|-------------------------------|------------------|
| TOLERANCE UNLESS OTHERWISE SPECIFIED | | DRAWN BY BETTY.YU | DATE 08-05-09 |
| DECIMALS | mm | CHECKED BY BETTY.YU | DATE 08-05-09 |
| X | ± 0.5 | APPROVED BY THOMAS | DATE 08-05-09 |
| X.X | ± 0.3 | U/M | mm |
| X.XX | ± 0.1 | | |
| ANGLES | ± 0.5° | | |

TITLE
**FLAT 6P4C,VOICE,S SATIN,XXFT
 (SEE TABLE I)**

THIS DRAWING WAS PRODUCED BY COMPUTER,
 DO NOT SCALE DRAWING OR UPDATE MANUALLY.

| | | |
|-----------------|--|-----------|
| SHEET 1 OF 1 | DRAWING NO. 32-1414-CUST (SEE TABLE I) | SIZE A |
|-----------------|--|-----------|

D

C

B

A

5

4

3

2

1

D

C

B

A