

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [02-08-2003](#)
Status: **Active**
Overview: [MLX™ Power Connectors](#)
Description: [MLX™ Crimp Terminal 42023, 14-20 AWG, Reel Tin \(Sn\)](#)

Documents:

[3D Model](#) [Product Specification PS-42022-0001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [42023](#)
Application [Power](#)
Crimp Quality Equipment [Yes](#)
Overview [MLX™ Power Connectors](#)
Packaging Alternative [02-08-2004 \(Loose\)](#)
Product Name [MLX™](#)
UPC [800753615656](#)

Physical

Gender [Male](#)
Material - Metal [Brass](#)
Material - Plating Mating [Tin](#)
Material - Plating Termination [Tin](#)
Net Weight [0.320/g](#)
Packaging Type [Reel](#)
Plating min - Mating [0.508µm](#)
Plating min - Termination [0.508µm](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [1.52-3.30mm](#)
Wire Size AWG [14, 16, 18, 20](#)
Wire Size mm² [N/A](#)

Material Info

Old Part Number [42023-2A1](#)

Reference - Drawing Numbers

Product Specification [PS-42022-0001](#)
Sales Drawing [SD-42023-****](#)



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[42023Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust™ Applicator for Crimp Terminals, 14-20 AWG Wire with 2.08-2.50mm Diameter Insulation	0639007500
FineAdjust™ Applicator for Crimp Terminals, 14-20 AWG Wire with 2.41-2.95mm Diameter Insulation	0639009900
T2 Terminator Tooling Die for Crimp	0639109800

Terminals, 14-20 AWG Wire FineAdjust™ Applicator for Crimp Terminals, 14-20 AWG Wire with 2.65-3.30mm Diameter Insulation	<u>0639009800</u>
T2 Terminator Tooling Die for Crimp Terminals, 14-20 AWG Wire	<u>0639109900</u>
Hand Crimp Tool for Pin and Socket Crimp Terminals	<u>0638116800</u>
Extraction Tool	<u>0011010168</u>
Tooling Kit for Mini- Fit Compliant Pin Insertion	<u>0639107500</u>

This document was generated on 01/28/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION