

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19221-0460

Status:


Active

Overview:

Battery Cable Lugs

Description:

Compression Style Ring Tongue Terminal for 4 AWG Wire, Stud Size 5/16" (M8), Plated, Wide Pad



Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-19901-017 \(PDF\)](#)

[Product Specification PS-19902-011 \(PDF\)](#)

[Product Specification PS-19902-013 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Ring and Spade Terminals
Series	19221
Comments	Heavy Duty
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	Battery Cable Lugs
Product Name	Battery Cable Lug
Type	Ring
UPC	800753065659

Physical	
Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	8.763/g
Packaging Type	Bag
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Stud Size	5/16" (M8)
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	N/A
Wire Size AWG	4
Wire Size mm²	96.3 - 117.0

Material Info	
Old Part Number	BCL-4516-WP-PL

Reference - Drawing Numbers	
Product Specification	PS-19901-017, PS-19902-011, PS-19902-013
Sales Drawing	SD-19221-010

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series	
19221Series	
Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals	0192940008
Manual Putt Pump Hydraulic System, Die set required	0192860117
Square "DIN" style dies for 4 AWG	0640037870
Die Set (large) for the HHLS Hydraulic Crimper	0192900007
Hand Crimp Tool	0192840034

This document was generated on 03/11/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION