


HAND HELD CASES

64 Series Handy Cases

Multi-purpose snap-fit hand-held enclosures designed for quick assembly.

- Moulded in high grade ABS, UL94-V0
- Snap-fit base & lid assembly, via end caps
- Battery compartment lid M3 retaining screw
- Recesses in lid, base and end caps for membrane keypads or overlays
- PCB pillars in lid and base
- Optional EPDM gasket for IP65 seal




Plastic End Caps

TYPE NO.	COLOUR	DESCRIPTION
CHH64E1BL	Blue - RAL 5007	to fit 20mm high cases
CHH64E1GR	Green - RAL 6026	to fit 20mm high cases
CHH64E1RD	Red - RAL 3020	to fit 20mm high cases
CHH64E1OR	Orange - RAL 2003	to fit 20mm high cases
CHH64E1BK	Black - RAL 9004	to fit 20mm high cases
CHH64E1YL	Yellow - RAL 1021	to fit 20mm high cases
CHH64E1DG	Grey - RAL 7001	to fit 20mm high cases
CHH64E2BL	Blue - RAL 5007	to fit 30mm high cases
CHH64E2GR	Green - RAL 6026	to fit 30mm high cases
CHH64E2RD	Red - RAL 3020	to fit 30mm high cases
CHH64E2OR	Orange - RAL 2003	to fit 30mm high cases
CHH64E2BK	Black - RAL 9004	to fit 30mm high cases
CHH64E2YL	Yellow - RAL 1021	to fit 30mm high cases
CHH64E2DG	Grey - RAL 7001	to fit 30mm high cases

SPECIFICATION	
Material	Lid & base high grade ABS, UL94-V0
Operating Temperature	Resistant to temperatures of up to 85°C
Protection class	IP62 as standard IP65 with gasket option
64 Series Standard colours	Top and base in grey RAL7035 and black RAL 9004. End caps-red, blue, yellow, green, orange, grey or black. Custom colours available to order
Standard unit includes	Top and base (Battery door & retaining screw size 2 & 4)
Options	End caps, battery compartments and gaskets supplied seperately IP65 gasket

BLACK	LIGHT GREY	LENGTH	WIDTH	HEIGHT	STYLE
CHH641NBK	CHH641NGY	100mm	80mm	20mm	-
CHH642BBK	CHH642BGY	100mm	80mm	30mm	battery door
CHH643NBK	CHH643NGY	120mm	80mm	20mm	-
CHH644BBK	CHH644BGY	120mm	80mm	30mm	battery door




64-IP Gasket

- EPDM rubber gasket
- IP65 protection
- Operating temperature -20°C to +85°C



TYPE NO.	DESCRIPTION
CHH64GASK	64-IP Gasket

Battery Compartments



TYPE NO.	DESCRIPTION	COLOUR
CHHBAT1BK	Clip-in Battery compartment PP3	Black
CHHBAT1GY	Clip-in Battery compartment PP3	Grey
CHHBAT2BK	Clip-in Battery compartment AA	Black
CHHBAT2GY	Clip-in Battery compartment AA	Grey

UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

19" CABINETS

DEVELOPMENT BOARD ENCLOSURES

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES