



		Copyright f	FCI.			
	\bigcirc			1	2	
PRODU	RODUCT NO. NO. OF POS		LOADED POS	HSG COLOR		
6183	1835–X441 4		ALL POS	BLACK		
-X421		4	3,4	BLACK		
-X442		4	ALL POS	GRAY		
	-X422 4		3,4	GRAY		
	PLATING CODE X		PLATING			
	0		5u" Au + high performance lubricant			
	1		15 ч"GOLD] (1)
	3		30 u "GOLD			\bigcirc
	4		6 ч"GOLD			
		5	50 ч "GOLD			
	٢			··· <u> </u>		۲.
	ļ		7.62			
Ø 3.25±0.08 (2X)						
		-				
			$' \qquad \qquad$			I
	:	35				:

Ø 0.76±0.08 (4X) \oplus ሐ 1.91 1.27 TYP BOARD LAYOUT VIEWED FROM TOP

1

FCIconnect.co

DIRECTION OF DISMOUNT

JACK DISMOUNT METHOD

DETAIL A

NOTE 5

2

9777



NOTES:



- 2 PACKAGING SPEC. GES-14-351. (USING TRAY).
- 3 SCRATCH MARKS ACCEPTABLE ON THESE SURFACES.
- 4 JACK IS FOR 1.57/.062 THICK PCB.
- 5 SHOULD THE JACK NEED TO BE DISMOUNTED FROM THE PCB. PLS REMOVE JACK AS PER RECOMMENDED METHOD HEREIN. (DETAIL A) NIPPING THE LEGS OF THE PEG TOGETHER IS DISALLOWED, OTHERWISE LEG BREAKAGE MAY OCCUR.
- 6 THESE DIMENSIONS ARE MEASURED FROM THE TOP OF THE PEG.
- 7 THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
- 8 IF LF P/N PACKSGING MEETS GS-14-920 SPECIFICATION
- 9 THE HOUSING WILL WITHSTAND EXPOSURE TO 260° PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD

/tolerance projectionproduct family

mm

scale2.0

FC

Ľ

selspecifiedtitle

(10) EQUIVALENT THICKNESS AU AND GXT PLATING HAVE SAME FUNCTION AND THEY ARE ALTERNATIVE BY THE CUSTOEMR .

89

В

D

Е

F

G

mat'l. code

ltrecn nødr date

sheet revision index sheet

N04-0023 D QIN 06/07/04

N04-0102 YS 11/23/04

N04-0109 YS 11/30/04 0°±2°

H ELX-N-010678SH MM0 03/14/12 engr TONY CHIEN

N08-0097 SH MM0 09/24/08 dr

XIIIIX

PDS: Rev :H 3

surface

ISD1302 V

angles

tolerances unless other 0.X±0.3

C L FENG

chr tony Chien

appd JENN TSAO

ISD1101 ISD406

02/21/97

02/21/97

02/21/97

02/21/97

0.XX±0.15

0.XXX±0.05

dwg no

type

MOD JACK

8 POS HORIZONTAL

P.C.B. III MOD JACK ASSY

Product Customer Drawing

61835

Printed: Sep 1242013

A4

В

sheet2of2 size

Α