

2-Port VGA/SVGA Video Splitter with Signal Booster, High Resolution Video, 350MHz, (HD15 M/2xF)

MODEL NUMBER: **B114-002-R**



Highlights

- Simultaneously displays video on 2 VGA/SVGA monitors
- A built-in booster allows a video signal (up to 2048 x 1536 @ 60Hz) to be transmitted up to 210 ft. from the source
- The splitter can be located up to 25 ft. from the connected computer, and up to 185 ft. from the connected monitors
- 350Mhz bandwidth support

System Requirements

- Computer with a HD15 port
- VGA/SVGA monitor
- The B114-002-R can only be cascaded to other B114-002-R splitters

Package Includes

- B114-002-R VGA/SVGA Video Splitter - 2 Port
- External power supply, 9V, 0.8A
- Owner's manual

Description

Tripp Lite's 2-Port VGA/SVGA Video Splitter provides bandwidth support at 350MHZ, allowing simultaneous display of video on 2 monitors. In addition, a built-in booster allows a video signal (up to 2048 x 1536 @ 60Hz) to be transmitted up to 210 ft. from the source. Two standard HD15 female ports are used to connect the monitors, while the a third HD15 male port is used to connect the CPU. The splitter can be located up to 25 ft. from the connected computer, and up to 185 ft. from the connected monitors. The number of connected monitors can be expanded by cascading up to 3 levels of B114-002-R splitters together.

Features

- Simultaneously display video on 2 VGA/SVGA monitors
- Ideal for video presentations or sharing information with multiple users
- A built-in booster allows a video signal (up to 2048 x 1536 @ 60Hz) to be transmitted up to 210 ft. from the source
- The splitter can be located up to 25 ft. from the connected computer, and up to 185 ft. from the connected monitors
- 350Mhz Bandwidth Support
- Cascade up to 3 levels of B114-002-R splitters together to increase the number of connected monitors
- Rugged, fully shielded metal housing

Specifications

General Info	
RoHS	Y
OVERVIEW	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Chromebook Compatible	No
Display Style	Splitter
Model Type	VGA
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	HD15 (MALE)
Connector B	HD15 (FEMALE) (X2)
Ports	2
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.