

# SLOTTED SCREWDRIVERS & SETS



Stock No. 58-0116

Set of 6 Slotted Drivers .025", .040", .055", .070", .080", .100"	OAL	Vinyl Pouch Stock No.	Canvas Roll Stock No.
with Steel Handles*	4"	58-0116	57-0116
with Fixed ESD-Safe Handles (short)	4.9"	58-0316	57-0316
with Interchangeable ESD-Safe Handles*	5.8"	58-0516	57-0516
with Mini Plastic Handles*	3.85"	58-0716	n/a
with Magnetic Handles*	4"	58-0816	57-0816

Please note: OAL = Overall Length including blade

Interchangeable Slotted Driver Set 6 Blades: .025", .040", .055", .070", .080" & .100"	OAL	Vinyl Pouch Stock No.	Clear Tube Stock No.
with 1 Steel Handle*	4"	58-0114	55-0114
with 1 Interchangeable ESD-Safe Handle*	5.8"		55-0314
with 1 Magnetic Handle*	4"	58-0175	55-0175
with 1 Mini Plastic Handle*	3.85"	58-0186	55-0186
w/ two 1/4" Hex Adapters (1 power, 1 insert)*	2.5", 3.18"	58-0265	55-0265



Stock No. 58-or 55-0175

Set of 8 Slotted Drivers with Fixed ESD-Safe Handles .025", .055", .070", .080" & .100"	OAL	Vinyl Pouch Stock No.	Canvas Roll Stock No.
.025", .055", .070", .080" & .100"	4.9"	58-0600	57-0600
.125", .141", .156"	6.2"		



Part of Stock No. 57-0600

Set of 5 Slotted Drivers with Fixed ESD-Safe Handles (long) .080", .100", .125", .141", .156"	OAL	Vinyl Pouch Stock No.	Canvas Roll Stock No.
.080", .100", .125", .141", .156"	6.2"	58-0415	57-0415

Slotted Individual Screwdrivers	OAL	0.025"	0.040"	0.055"	0.070"	0.080"	0.100"	0.125"	0.141"	0.156"
		(0.6mm) Stock No.	(1.0mm) Stock No.	(1.4mm) Stock No.	(1.8mm) Stock No.	(2.0mm) Stock No.	(2.5mm) Stock No.	(3.2mm) Stock No.	(3.5mm) Stock No.	(4.0mm) Stock No.
Steel*	4"	51 or 76 -1522	51 or 76 -1523	51 or 76 -1524	51 or 76 -1525	51 or 76 -1526	51 or 76 -1527	51 or 76 -1787	Available in 6.2"	Available in 6.2"
Fixed ESD-Safe Handle (short)	4.9"	51 or 76 -2022	51 or 76 -2023	51 or 76 -2024	51 or 76 -2025	51 or 76 -2026	51 or 76 -2027	51 or 76 -2028	ESD-Safe Only	ESD-Safe Only
Fixed ESD-Safe Handle (long)	6.2"	Not Available	Not Available	Not Available	Not Available	51 or 76 -2001	51 or 76 -2002	51 or 76 -2003	51 or 76 -2004	51 or 76 -2005
Interchangeable ESD-Safe Handle*	5.8"	51 or 76 -2120	51 or 76 -2121	51 or 76 -2122	51 or 76 -2123	51 or 76 -2124	51 or 76 -2125	51 or 76 -2126	Available in 6.2"	Available in 6.2"
Magnetic Handle*	4"	51 or 76 -1595	51 or 76 -1596	51 or 76 -1597	51 or 76 -1598	51 or 76 -1599	51 or 76 -1600	51 or 76 -1789	ESD-Safe Only	ESD-Safe Only
Plastic Handle*	3.85"	51 or 76 -1625	51 or 76 -1626	51 or 76 -1627	51 or 76 -1628	51 or 76 -1629	51 or 76 -1630	51 or 76 -1788		
Blade Only**	1.8"	49-8006	49-8007	49-8008	49-8009	49-8010	49-8011	49-8018		

Please see our selection of Reversible Drivers on page 9 for even more Slotted sizes.

\* These Screwdrivers have interchangeable blades.

\*\* Interchangeable replacement blades fit into Steel, Magnetic, Mini Plastic & Interchangeable ESD-Safe handles (see pg. 35).

Note: 51- notates individually packaged in a hanging poly bag, 76- notates packaged 10 to a box. See page 36 for more info.

Many Moody Tools have **National Stock Numbers**;

Set **58-0116** is NSN's 5120-00-288-8739; 5120-01-333-9833; 5120-01-119-2570.

Set **58-0114** is NSN 5120-01-135-2993. See the **NSN Index on page 34** for equivalencies.

