



REV.	MODIFICATION.	DATE	DRN
01	NEW DRAWING	18/10/04	NJB
02	ECN05-026	03/02/05	OW
03	ECN05-056	27/04/05	OW
04	ECN06-227	03/10/06	NJB
05	CO2010988	09/09/10	SF
06	CO2011223	20/12/11	SF



PART REF:	L							D	K				
NSE-1207-M2-L	4.0[.158]	5.0[.197]	6.0[.236]	8.0[.315]	10.0[.394]	12.0[.473]	16.0[.630]	20.0[.788]	25.0[.985]			3.8[.149]	1.4[.055]
NSE-1207-M2.5-L	6.0[.236]						15.0[.591]		-			4.5[.177]	1.8[.070]
NSE-1207-M3-L	4.0[.158]	5.0[.197]	6.0[.236]				16.0[.630]		25.0[.985]	30.0[.182]	40.0[.575]	5.5[.216]	2.0[.078]
NSE-1207-M4-L	6.0[.236]						-		-	-	-	7.0[.275]	2.6[.102]
NSE-1207-M5-L												8.5[.334]	3.3[.129]
NSE-1207-M6-L												10.0[.394]	3.9[.153]

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT

**RICHCO, INC.**  
WWW.RICHCO-INC.COM

GENERAL TOLERANCES ±0.25 [0.010] ARE FOR REFERENCE UNLESS OTHERWISE  
1 DECIMAL PLACE ±  
2 DECIMAL PLACES ±  
ANGULAR ±1°

MATERIAL: **NYLON 6/6 (RMS-179)** COLOUR: **NATURAL**

TITLE: **METRIC SCREW (DIN EN ISO 1207)** PART No: **NSE-1207-MX-L**

DRG No: **04-114** NPR REF:

DRN: **NJB** DATE: **18/10/04** CHKD: **I.C** DATE: **18/10/04** SCALE: **NTS** SHEET No: **1 OF 1**

NOTES:  
 1a) Metric primary units:mm.  
 b) Imperial secondary units: [Inches].  
 2 Parts available in Colour Black by special order:  
 Add "BK" to end of part number.  
 Example: NSE-1207-M4-8BK

ALTERNATE UNITS FOR REFERENCE ONLY