

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [47535-0001](#)
Status: **Active**
Overview: SIM - Smart Card Connectors
Description: 2.54mm Pitch SIM Card Connector, Dome Contacts, Block Style, 6 Circuits, Housing Height: 0.95mm, Solderetail Height: 0.05mm, Halogen-free

Documents:

[3D Model](#) [Product Specification PS-47535-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Memory Card Sockets
Series	47535
Comments	Housing Height: 0.95mm; Solderetail Height: 0.05mm
Component Type	Header/Socket (Host)
Overview	SIM - Smart Card Connectors
Product Name	Block SIM
Style	Block
Type	N/A
UPC	800756650548

Physical

Card Detection Switch	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	500
Ejector Button	No
Ejector Button Side	N/A
Entry Angle	Horizontal, Side Entry, Vertical
Keying to Mating Part	None
Material - Metal	Beryllium Copper
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	0.188/g
PCB Locator	No
PCB Mounting Side	Normal
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.762µm
Plating min - Termination	0.051µm
Ports	0
Temperature Range - Operating	-20°C to +70°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	0.5A
Shielded	No
Voltage - Maximum	15V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	3
Lead-free Process Capability	Reflow Capable (SMT only)



*Series
image - Reference only*

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[47535Series](#)

Mates With

Micro-SIM Card

Use With

Micro-SIM Card

Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	255

Material Info

Reference - Drawing Numbers

Product Specification	PS-47535-001
Sales Drawing	SD-47535-001

This document was generated on 12/29/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION