

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2006

© COPYRIGHT 2006

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

LOC
A1DIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D3	ECR-11-015098	20JUL2011	GW	OH

2

Notes

- SUITABLE HOUSINGS: SERIES HC26
CUSTOMER DRAWING: 1103439, 1103436
- SUITABLE INSERTS: SERIES HC26
CUSTOMER DRAWING: 1103428, 1103429,
1103431, 1103432
- STANDARDS:
DIN EN 61984, DIN EN 60664-1
- PACKAGING:
40 SETS IN A CARTON
- SUITABLE: ACCESSORY KIT:
CUSTOMER DRAWING 1103519

PN 0-1 AS SHOWN

2	SCREW FOR METAL	STEEL	ZINC PLATED	10
1	CLIP TAB	STEEL	ZINC PLATED	9
1	COVER	ZINC ALLOY	NICKEL PLATED	8
1	COUPLING NUT	ZINC ALLOY	NICKEL PLATED	7
1	CONNECTOR ADAPTOR	ZINC ALLOY	NICKEL PLATED	6
1	CIRCULAR HOUSING	ZINC ALLOY	NICKEL PLATED	5
1	SCREW, PAN HEAD	STEEL	NICKEL PLATED	4
2	RETAINING RING	PA66-GF25	GREY	3
1	SEALING	FKM	GREY	2
1	O-RING	FKM 70	BLUE	1
QTY	DESCRIPTION	MATERIAL	SURFACE/COLOR	ITEM

PARTS LIST (PER ONE UNIT)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 24SEP2009

T.VETTER

CHK 24SEP2009

O.HOLZMANN

APVD 24SEP2009

T.SCHNURPFEL

PRODUCT SPEC

108-74097

APPLICATION SPEC

114-74103

WEIGHT

-

CUSTOMER DRAWING

DIMENSIONS:

mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±1°
FINISH	-

FINISH

-

24SEP2009

24SEP2009

24SEP2009

NAME

T.SCHNURPFEL

PRODUCT SPEC

108-74097

APPLICATION SPEC

114-74103

WEIGHT

-

CUSTOMER DRAWING

DWN 24SEP2009

CHK 24SEP2009

APVD 24SEP2009

NAME

T.SCHNURPFEL

PRODUCT SPEC

108-74097

APPLICATION SPEC

114-74103

WEIGHT

-

CUSTOMER DRAWING

SCALE 1:1

SHEET 1 OF 1

REV D3

TE Connectivity

OBsolete

CONNECTOR HOUSING ASSY
SERIES HC26, CIRC. HSG., DESIGN METAL
POWER 4 NET

SIZE A3 CAGE CODE 00779 DRAWING NO. C-1103440 RESTRICTED TO

NOT the LATEST REVISION

1470-19 (3/11)

Pro/ENGINEER DRAWING