

## **Knockdown Steel 2-Post Robust Rack** *DNRRLDK Series* Front 10-32 Tapped Rails



When strength and reliability is the highest priority, be sure to choose the Data/Networking Robust Rack (DNRR) from Hammond Manufacturing. Designed to support your rack mount infrastructure, regardless of the application, the DNRR includes premium features not found on most other racks.

### **Features**

- Constructed in 12-gauge steel..
- Tested to nearly double the suggested load rating of 800 lbs, Hammond engineered the DNRR\*\*LDK to exceed your weight requirements.
- Our automated tapping assembly provides EIA-310-D compliant 10-32 tapped rails on the front to ensure ease of mounting rack mount equipment.
- To keep the rack upright when loaded with equipment, we've included a large base for freestanding support. Optionally, the base can be caster mounted for moving the rack.
- To keep it looking great, the DNRR undergoes a three-stage paint process which includes a coat of premium smooth black powder paint.
- Before sending the DNRR on its way we package the parts securely in a thick cardboard carton to prevent any damage that may occur during transportation.
- RoHS Compliant.
- Manufactured in North America.

### **Accessories**

- Universal Rack Shelf
- Two Post Mounting Adjustable Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- Outlet Strips
- Cable Management
- 10-32 Countersunk Rack Screw with Plastic Cup Washer
- Small Head 10-32 Thumb Screw
- Rack Panels
- Rack and Cabinet Baying/Ganging/Joining Kit
- Two Post Mounting Clamping Shelf
- Two Post Centered Shelf
- Adjustable Depth DIN Rail Panel
- Hinged Acrylic Door Panel Cover
- 10-32 Black Rack Screw with Nylon Washer
- 10-32 Rack Screws with Pilot Point
- Grounding
- Rack Unit Label

Part No.	Overall Dimensions			Mounting Dimensions			
	Height	Width	Depth	Height	Width	Rack Units	Wt. lbs.
<b>DNRR1942LDK</b>	45.00	20.00	19.81	42.00	19.00	24U	38
<b>DNRR1963LDK</b>	66.00	20.00	19.81	63.00	19.00	36U	41

Part No.	Overall Dimensions			Mounting Dimensions			Wt. lbs.
	Height	Width	Depth	Height	Width	Rack Units	
<b>DNRR1970LDK</b>	73.00	20.00	19.81	70.00	19.00	40U	42
<b>DNRR1977LDK</b>	80.00	20.00	19.81	77.00	19.00	44U	45
<b>DNRR1984LDK</b>	87.00	20.00	19.81	84.00	19.00	48U	47

*Data subject to change without notice*

© 2015. Hammond Manufacturing Ltd. All rights reserved.