

JIS-TYPE S DRIVERS & SETS


Set of 4 JIS-Type S Drivers #000(.055"), #00(.080"), #0(.100"), #1(.125") with Steel Handles*	OAL	Vinyl Pouch Stock No.
with Fixed ESD-Safe Handles (short)	4.9"	58-0319
with Fixed ESD-Safe Handles (long)	6.2"	58-0405
with Interchangeable ESD-Safe Handles*	5.8"	58-0519
with Mini Plastic Handles*	3.85"	58-0719
with Magnetic Handles*	4"	58-0819



Set of 8 JIS-Type S Drivers with Fixed ESD-Safe Handles	OAL	Vinyl Pouch Stock No.	Canvas Roll Stock No.
#000(.055"), #00(.080"), #0(.100"), #1(.125")	4.9"	58-0610	57-0610
#000(.055"), #00(.080"), #0(.100"), #1(.125")	6.2"		

Interchangeable JIS-Type S Driver Set 4 Blades: #000(.055"), #00(.080"), #0(.100"), #1(.125")	OAL	Vinyl Pouch Stock No.	Clear Tube Stock No.
with 1 Steel Handle*	4"	58-0218	55-0218
with 1 Interchangeable ESD-Safe Handle*	5.8"	58-0318	55-0318
with 1 Magnetic Handle*	4"	58-0221	55-0221
with 1 Mini Plastic Handle*	3.85"	58-0222	55-0222
w/ two 1/4" Hex Adapters (1 power, 1 insert)*	2.5", 3.18"	58-0262	55-0262


Interchangeable Cross Point Driver Set 4 Blades: JIS #000(.055"), #00(.080") & Phil #0(.100"), #1(.125")	OAL	Vinyl Pouch Stock No.	Clear Tube Stock No.
with 1 Steel Handle*	4"	58-0200	55-0200
with 1 Interchangeable ESD-Safe Handle*	5.8"	58-0300	55-0300
with 1 Magnetic Handle*	4"	58-0203	55-0203
with 1 Mini Plastic Handle*	3.85"	58-0204	55-0204
w/ two 1/4" Hex Adapters (1 power, 1 insert)*	2.5", 3.18"	58-0264	55-0264



What's the difference between Phillips and JIS?

These cross-point drivers appear deceptively similar to one another. Phillips is the type with which most people are familiar. JIS (Japanese Industrial Standard) drivers will always fit Phillips fasteners, but because of slight design differences, Phillips drivers may not fit JIS fasteners. (see illustration below).

JIS-Type S Individual Screwdrivers	OAL	#000 Stock No.	#00 Stock No.	#0 Stock No.	#1 Stock No.
Steel Handle*	4"	51 or 76 -1663	51 or 76 -1664	51 or 76 -1785	51 or 76 -1786
Fixed ESD-Safe Handle (short)	4.9"	51 or 76 -2063	51 or 76 -2064	51 or 76 -2085	51 or 76 -2086
Fixed ESD-Safe Handle (long)	6.2"	51 or 76 -2403	51 or 76 -2400	51 or 76 -2401	51 or 76 -2402
Interchangeable ESD-Safe Handle*	5.8"	51 or 76 -2143	51 or 76 -2142	51 or 76 -2141	51 or 76 -2140
Magnetic Handle*	4"	51 or 76 -1665	51 or 76 -1666	51 or 76 -1777	51 or 76 1778
Plastic Handle*	3.85"	51 or 76 -1667	51 or 76 -1668	51 or 76 -1781	51 or 76 -1782
Blade Only**	1.8"	49-8070	49-8071	49-8072	49-8073



* These Screwdrivers have interchangeable blades.

** Interchangeable replacement blades fit into Steel, Magnetic, Mini Plastic & Interchangeable ESD handles (shown on pg. 35).

Note: 51- notates individually packaged in a hanging poly bag, 76- notates packaged 10 to a box. See back cover for more info.

