



Integrity® Cleanroom

Integrity® Pre-Saturated Wipe Tub

Ideal for Cleanroom/Medical environments, the wipes are pre-saturated with a 70% vv solution of Isopropyl alcohol BP and are effective against gram-negative bacteria, fungi and most viruses. Microorganisms include E.coli, MRSA, Listeria, Salmonella, HIV and TB.

FEATURES AND BENEFITS

- Broad Spectrum Activity
- Fast contact time
- Low lint wipes
- Available sterile by Gamma Irradiation

APPLICATION

- Disinfection on all types of hard surfaces
- Use in ISO6-1S07 Cleanrooms

WIPE SIZE & QUANTITY	200mm x 200mm; 200 wipes
COLOUR	White
WEIGHT	18gsm +/- 7.5%
WIPE MATERIAL	Continuous filament thermo bonded nonwoven 100% PP
HYDROPHILIC SOLUTION	70% Isopropyl alcohol (IPA)
ACTIVE INGREDIENTS	70% Isopropyl alcohol (weight/weight)



TESTING:

Proven as active against gram positive and gram-negative bacteria, as well as most viruses, fungi and micro-organisms. Test data available

AREAS OF USE:

Disinfectant and cleaning hard surfaces, machinery, utensils and equipment in potentially sensitive areas – primarily healthcare, clinical and pharmaceutical production environments.

PACKAGING:

2000ml HDPE canister with flip-top lid 12 canisters per outer case (565 x240 x 255mm) Weight of carton 7.83kg 42 outer cases per (Euro) pallet

BENEFITS OF USE:

Controlled delivery of disinfectant; no premixing/ waste; non-tainting; dermatological tested; single use; portable.

Call +44 (0) 1473 836205 Email info@integritycleanroom.com [/integrity_eu](https://twitter.com/integrity_eu) [/company/integrity-cleanroom](https://www.linkedin.com/company/integrity-cleanroom)

IMPORTANT NOTICE: This data sheet and its contents (the "Information") belong to Integrity® Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity® Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity® Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity® Cleanroom.





Integrity® Cleanroom

PHYSICAL PROPERTIES	UNIT	TARGET	MIN OR MAX	TEST METHOD
Basis Weight 18 WRP	g.	18	±7,5%	130.1 (05)
Tensile strength MD	N/5cm	38	>28,5	WSP 110.4 (05) Option B Jaw distance 100 mm Rate of extension 200mm/min without pretension
Tensile strength CD	N/5cm	22	>16,5	
Elongation at 10N	%	-----	±1 Value	
Elongation MD	%	70	>52	
Elongation CD	%	70	>52	
Absorptive Capacity	%	450	>330	*WSP10.1(05)
Sinking Time	Sec.	25	>35	10.1(05)A
Thickness	mm.	0,2	>0,15:<0,30	*WSP 120.6 (05)
Nonwovens sampling				*WSP 5.0 -05

PRODUCT CODE 600-0012

Call +44 (0) 1473 836205 Email info@integritycleanroom.com  /integrity_eu  /company/integrity-cleanroom

IMPORTANT NOTICE: This data sheet and its contents (the "Information") belong to Integrity® Cleanroom or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Integrity® Cleanroom assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Integrity® Cleanroom was aware of the possibility of such loss or damage arising) is excluded. © Integrity® Cleanroom.

