



Integrity® Cleanroom

Integrity® Blue Sponge Cleanroom Mop Head 600-1000

The Foam Mophead is manufactured from a fine-pore polyurethane foam. Designed for cleaning and disinfecting all types of controlled environments. Exceptional abrasion and tear resistance.

FEATURES AND BENEFITS

- It can be used on floors, walls and ceilings
- Complies with ROHS Directive 2002/95/EC
- Can be used in conjunction with M01 polyester cover
- Available in sterile form by Gamma Irradiation

APPLICATIONS

- Ideal for cleaning and disinfecting applications requiring high absorbency and very low particulate generation
- Perfect for cleanrooms, laboratories and any other dust/dirt free environment
- Biotechnology & Pharmaceutical industries and other non-critical environments

PHYSICAL CHARACTERISTICS

MATERIAL COMPOSITION	COLOUR	MOP DIMENSION	THICKNESS	GSM	ABSORBENCY CAPACITY	HARDNESS	DENSITY	HARDNESS
Polyurethane foam	Blue	40 cm x 13 cm	Top: 10mm Bottom: 15mm	Top: 260 Bottom: 374	4,170 ml/m ² 6,246 ml/m ²	50 + 3	19 + 1 kg/m ³	50 + 3

To be used with:

- 600-1007 Mop Frame
- 600-1008 Extension Pole
- 600-1001 Polyester Cover
- 600-1006 Polyester Cover Sterile
- 600-1002 Disposable Mop Heads (Poly Cellulose)
- 600-1003 Disposable Mop Heads (Polyester)

PRODUCT CODES	QTY
600-1000	Pack of 5
600-1005 Sterile	Pack of 5



Call +44 (0) 1473 836205 Email info@integritycleanroom.com [/integrity_eu](https://twitter.com/integrity_eu) [/company/integrity-cleanroom](https://www.linkedin.com/company/integrity-cleanroom)

IMPORTANT NOTICE: This data sheet and its contents (the "Information") belong to the Integrity or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The information is subject to change without notice and replaces all data sheets previously supplied. The information supplied is believed to be accurate but the Integrity assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the information or use of it (including liability resulting from negligence or where the Integrity was aware of the possibility of such loss or damage arising) is excluded. © Integrity.

