



Integrity[®] Cleanroom

Integrity[®] Facemask with Earloops

FEATURES AND BENEFITS

- Cleanroom processed and packaged to reduce particles
- Silicon-free and lint-free blue Polyurethane loop
- Ultra-low lint and contamination level
- Solvent-safe, cleanroom double-bagged packaging
- Hypoallergenic-soft surface layers that prevents skin irritation and allergy problems
- Ultrasonic bonding reduces contamination & outgassing
- Extra wide (210mm) provides maximum facial coverage and reduces exposed skin

SPECIFICATIONS

- Loop can be customized to earloop or headloop type
- Mask dimension is available in 180 mm x 90 mm, 210 mm x 90 mm



OUTER FACIAL LAYER:	Combined Polymer ES - 17 gsm
FILTER CENTER LAYER:	Meltblown Polypropylene -18 gsm
INNER FACIAL LAYER:	Combined Polymer ES - 17 gsm
NOSE PIECE:	Metal stripped with coating
LOOP MATERIAL	White OP Earloop/Headloop

MASK MATERIAL CHARACTERISTICS

TEST	RESULT
BACTERIAL FILTRATION EFFICIENCY (BFE) (3.0UM) (ASTM F 2102)	95.10%
PARTICLE FILTRATION EFFICIENCY (PFE) (0.1um) (ASTM F 2299)	97.60%
AIRBORNE PARTICLE COUNT (HELMKE DRUM) (>0.5um) (IEST-RP-CC003.2)	70 counts/pc./cfm

PLEASE NOTE

Data shown are typical values and should not be used as specifications.

PRODUCT CODE	PACK QUANTITY
600-3001	100 - Bulk Pack
600-3006	Individual Bag Pack of 20
600-3006G	20 pack - STERILE

Call +44 (0) 1473 836205 Email info@integritycleanroom.com [/integrity_eu](https://twitter.com/integrity_eu) [/company/integrity-cleanroom](https://www.linkedin.com/company/integrity-cleanroom)

IMPORTANT NOTICE: This data sheet and its contents (the "Information") belong to the Integrity or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Integrity assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Integrity was aware of the possibility of such loss or damage arising) is excluded. © Integrity.

