Tripp Lite

1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

SmartRack 6U Wall-Mount Standard-Depth Rack Enclosure Cabinet, Black

MODEL NUMBER: SRW6U











Description

Tripp Lite's SRW6U Wall Mount Rack Enclosure Cabinet is the ideal storage solution for standard rackmount equipment in applications with limited floor space such as wiring closets, POS stations and offices. Constructed with a sturdy wall mounting bracket and steel frame, it can accommodate up to 140 lbs. of equipment in 6U of rack space. Adjustable vertical mounting rails with square holes accommodate all standard 19-inch rack equipment.

The SRW6U features a perforated lockable front door and side panels, assuring generous airflow to keep equipment operating safely. The side panels are removable for easy access to equipment, and the front door is reversible. The top and bottom panels of the enclosure include convenient cable routing ports. The SRW6U ships fully assembled and comes with a 5-year manufacturer's product warranty.

Features

- 6U wall-mounted enclosure
- Ideal for VoIP wiring closets and education venues that require security
- Adjustable mounting depths up to 17" by 2 front vertical rackmount rails
- · Ventilated front door and side panels for increased airflow
- Locking, reversible front door
- · Locking, removable side panels
- · Fully assembled for quick installation
- . Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

Specifications

General Info

Highlights

- Designed for VoIP closets and education environments where equipment needs to be secure and out of the way
- 6U with adjustable front vertical rackmount rails
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard)
 Compliance
- Interior vertical posts have square holes for cage nuts plus 12-24 threaded mounting holes

Applications

IT network environments with limited floor space, VoIP closets, and classrooms where equipment needs to be secure and out of the way of students.

Package Includes

- SRW6U Wallmount Rack Enclosure
- (12) M6 screws
- (12) M6 cage nuts
- (12) M6 washers
- (2) Keys
- Owner's Manual



RoHS	Y
OVERVIEW	
Style	Wall Mounted
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	16.5
Installed Whole System Maximum Rack Depth (cm)	41.9
Installed Whole System Minimum Rack Depth (in.)	3
Rack Height (U Spaces)	6
Shipping Dimensions (hwd / in.)	17.5" x 26.5" x 20.5"
Shipping Dimensions (hwd / cm)	44.45 x 67.31 x 52.07
Shipping Weight (lbs.)	32
Shipping Weight (kg)	14.5
Unit Dimensions (hwd / in.)	14.5 x 23.63 x 17.5
Unit Weight (lbs.)	29
Unit Weight (kg)	13
Unit Dimensions (cm)	36.83 x 60.02 x 44.45
Color	Black
Weight Capacity - Stationary (lbs.)	200
Weight Capacity - Stationary (kg)	90.7
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Hinged (Swings Away from Wall Bracket)	No
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames
CERTIFICATIONS	
Certifications	EIA-310-E
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)

5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.