



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Universal Reversible USB 2.0 Hi-Speed Cable (Right/Left Angle Reversible A to Reversible A M/M), 6-ft.

MODEL NUMBER: **UR020-006-RA**



Highlights

- 6ft, USB 2.0, Right / Left Angle Male-to- Straight Male
- Universal, Reversible connector allows plugging in any direction

System Requirements

- Computer with USB A-Female port
- USB device or Patch port with USB A-Female port

Package Includes

- 6ft, USB 2.0, Right / Left Angle Male-to-Straight Male Universal / Reversible Cable

Description

Easily connect USB devices without fumbling with the connector. Tripp Lite Reversible USB cables have connectors that work in either direction, so you don't have to look to see which is right-side-up anymore.

Notes:

1. USB Male-to-Male cable is not a standard USB cable configuration, and is only used in rare instances where a peripheral or patch bay employs a USB A-Female connection, in place of USB B-type port.
2. This cable will not work as a PC-to-PC connection. File sharing between computers requires special, software-driven file transfer cables, such as Tripp Lite [U233-006-PP-R](#) or [U233-006-MP-R](#).

Features

- 6ft USB 2.0 Right / Left Angle Male-to-Straight Male, with Universal / Reversible connectors
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold contacts and molded ends provide a lifetime of use

Specifications

General Info	
RoHS	Y
OVERVIEW	
Chromebook Compatible	Yes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Style	USB
Cable Types	USB
OUTPUT	
USB Charging	No
INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.91
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
CONNECTIONS	
Connector A	REVERSIBLE USB A (MALE)
Connector B	REVERSIBLE USB A (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.