

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002092118](#)
Status: **Active**
Overview: Standard .093" Pin and Socket Connectors
Description: 2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Tin (Sn) Plated Brass Contact, 18-22 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-02-09 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	1380
Application	Power
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	Standard .093" Pin and Socket Connectors
Packaging Alternative	02-09-2116 (Reel)
Product Name	Standard .093"
UPC	800753746114

Physical

Durability (mating cycles max)	25
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.206/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size AWG	18, 20, 22
Wire Size mm ²	N/A

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Old Part Number	1380-(P901)L
-----------------	--------------

Reference - Drawing Numbers

Product Specification	PS-02-09
Sales Drawing	SD-1380-*



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(17.
December 2014): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[1380 Series](#)

Use With

[1619 Plug or Receptacle Housing](#),
[1545 Plug or Receptacle Housing](#), [1396 Plug or Receptacle Housing](#), [1490 Plug or Receptacle Housing](#), [2629 Plug or Receptacle Crimp Housings](#), [1261 Plug or Receptacle Housing](#), [1292 Plug or Recept](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Extractor Tool
for .093 and

Product #

[0638240200](#)

HCS-125 Product Series	
Hand Crimp Tool	<u>0638191200</u>
Insertion Tool	<u>0011020003</u>
Extraction Tool	<u>0011030006</u>

This document was generated on 06/22/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION