Product Data Sheet

3M™ Heel Grounder Non-Marking NS-HGC1M Blue

The blue sole of the Non-Marking Heel Grounder NS-HGC1M eliminates scuff marks on ESD floors. The re-positionable configuration extends the life of the product and the elastic loop provides a secure and comfortable fit. This quality grounder is tested for electrical performance and is lot numbered.





Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive Sanford, NC 27332-9733 Toll-Free: 866-722-3736 International: 919-718-0000 Email: 3mstaticinfo@mmm.com www.3Mstatic.com

Please recycle. Printed in USA.
© 3M 2014. All rights reserved.
78-9102-1615-5 JHA

may come in contact with electrical circuitry

exceeding 250 volts.

Specifications	Typical Value
Elastic Hook and Loop	3/4", elastic loop, black
Traceability	Lot coded
Sole Exterior	<108 ohms
Total Grounder*	10 ⁶ - 10 ⁸ ohms

^{*}Meets the requirements of ANSI/ESD S20.20-2014, EIA 625, UL

Part Numbers

How Heel Grounders Work

Heel grounders eliminate a charge on a person by electrically connecting the person to a grounded surface. A conductive ribbon placed inside the wearer's shoe or sock makes electrical contact with the skin through perspiration. The assembly contains a current-limiting resistor which protects the operator from accidental exposure to electricity. Heel grounders must be worn on both feet to maintain ground contact while walking.

3M is a trademark of 3M Company. All other trademarks are owned by their respective companies.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.