

# HAND HELD CASES

## 87 Series Silicone Cover Enclosure

Hand-held Enclosure, suitable for measuring instruments, testing devices, wireless communication devices, medical devices etc.

- Silicone cover accessory available
- Available in six sizes, with or without moulded battery compartments. (further battery compartment options available upon request)
- Recess to front for keypads and labels
- Removable end panel
- Battery contacts supplied
- Available in two colours: off-white & dark grey

SPECIFICATION	
Materials	Lid & base high impact ABS-UL94-V0
Operating temperature	-10°C to +60°C
Standard colours	Off-White & Dark grey
Standard unit includes:	Lid and Base, self-tapping screw
Options	Silicon case in red, yellow, blue and dark grey

**TAKACHI**



### Without Battery Compartment


SIZE	DARK GREY	OFF-WHITE	LENGTH	WIDTH	HEIGHT
1	CHH871DGN	CHH871WHN	115mm	69mm	19.5mm
2	CHH872DGN	CHH872WHN	115mm	69mm	28mm
3	CHH873DGN	CHH873WHN	135mm	76mm	27mm
4	CHH874DGN	CHH874WHN	135mm	76mm	35mm
5	CHH875DGN	CHH875WHN	165mm	80mm	27mm
6	CHH876DGN	CHH876WHN	165mm	80mm	35mm

### With Battery Compartment

SIZE	DARK GREY	OFF-WHITE	LENGTH	WIDTH	HEIGHT	BATTERY COMPARTMENT
1	CHH871DGA	CHH871WHA	115mm	69mm	19.5mm	2 x AAA
2	CHH872DGB	CHH872WHB	115mm	69mm	28mm	2 x AA
3	CHH873DGB	CHH873WHB	135mm	76mm	27mm	2 x AA
4	CHH874DGB	CHH874WHB	135mm	76mm	35mm	2 x AA
5	CHH875DGC	CHH875WHC	165mm	80mm	27mm	4 x AA
6	CHH876DGC	CHH876WHC	165mm	80mm	35mm	4 x AA

### Silicone Cover

- Flexible open faced removable silicon rubber cover
- Fits tightly over base, sides and around edges of lid
- Custom colours available from MOQ 500 pcs per order, just provide us with your pantone colour
- Rubber boots can be customised
- Ruggedised boots available on request



SIZE	RED	YELLOW	BLUE	DARK GREY	LENGTH	WIDTH	HEIGHT	DESCRIPTION
1	CHH87C1RD	CHH87C1YL	CHH87C1BL	CHH87C1DG	120mm	74mm	24mm	Fits Enclosure size 1
2	CHH87C2RD	CHH87C2YL	CHH87C2BL	CHH87C2DG	120mm	74mm	32.5mm	Fits Enclosure size 2
3	CHH87C3RD	CHH87C3YL	CHH87C3BL	CHH87C3DG	141mm	81mm	32mm	Fits Enclosure size 3
4	CHH87C4RD	CHH87C4YL	CHH87C4BL	CHH87C4DG	141mm	81mm	40mm	Fits Enclosure size 4
5	CHH87C5RD	CHH87C5YL	CHH87C5BL	CHH87C5DG	171mm	85mm	32mm	Fits Enclosure size 5
6	CHH87C6RD	CHH87C6YL	CHH87C6BL	CHH87C6DG	171mm	85mm	40mm	Fits Enclosure size 6



+44 (0)1638 716101  
info@camdenboss.com  
www.camdenboss.com

We operate a constant improvement policy, our products are subject to change without notice. Ver 1.0 Iss 4

**CAMDENBOSS**  
ELECTRONICS & ENCLOSURES

UNIVERSAL ENCLOSURES

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL BOXES

INTERFACE SUPPORTS

CONTROL STATIONS

DIECAST & METAL BOXES

DESKTOP & INSTRUMENT CASES

POTTING BOXES

19" ENCLOSURES

19" CABINETS

DEVELOPMENT BOARD ENCLOSURES

CUSTOM SIZED ENCLOSURES

CUSTOM SERVICES