

Doro Secure 580IUP

Mobile phone with Isolated User Protection

Need a phone that can automatically alert someone in the case of a fall or a motionless state? This durable and splash proof (IP54) mobile provides excellent isolated user protection through mandown, motionless and self-activated alert functions. It also features GPS localization to let people know where they can find you. Ideal for anyone who works alone in potentially dangerous environments.

- ✔ Automatic and self-activated alert
- ✔ Detects fallen and motionless states
- ✔ GPS localization



STANDARD FEATURES ON MOST DORO PHONES

- | | | | | | | | | |
|--|---|---|---|---|---|--|---|---|
|  |  |  |  |  |  |  |  |  |
| Loud and clear sound | Adjustable frequency | Hearing Aid Compatible | Separated large keys | Adjustable contrast and theme | Security functions | Ergonomic design | Easy menu handling | Hide unwanted functions |

Doro Secure 580IUP



Main features

Speakerphone	✓
Keylock	✓
Backlit keypad	✓
Key tone	✓
Startup wizard	✓
Assistance button	✓
Safety timer	✓
IP-classification	IP54
ICE (In Case of Emergency)	✓

Memories

Call log positions	20
One touch memories	4
Phonebook positions	4

Handset unit display

Colour display	✓
Display size (H x W mm)	28*35
Resolution (H x W pixels)	128*160
Big display text	✓
Optional display modes optimised for visually impaired users	✓

SMS

Receive-only SMS	✓
Assistance SMS with GPS position	✓
Message opened receipt	✓

Sounds & Signals

Polyphonic ringtones	20
Visual ring indicator	✓
Vibrating ringer	✓

Hearing Aid Compatibility Rating T4/M4 (3G), T3/M3 (GSM)

Maximum ringer volume (dB(A) at 1 metre)	>87
Volume settings	7
Tone control	✓
HD voice certified	✓

Ergonomics

Hide unwanted functions	✓
Separated keys	✓
Handset size (mm)	127*56*15
Handset weight including batteries (g)	100
Soft touch coating for better grip	✓

Cables & Connections

Headset outlet (3.5mm)	✓
------------------------	---

Powering handset unit

Standby time (up to hours)	350
Talk time (up to hours)	10
Battery included (type)	800mAh Li-ion
AC Adapter spec V/mA	5V/500mA
Universal Charging solution (UCS)	✓

Technology

GSM (band)	900/1800/1900
3G	✓
3G (Bands)	UMTS Band 1 (2100) & 8 (900)
Bluetooth®	✓
Bluetooth® protocol	2.1

Accessories

Charging cradle included	✓
--------------------------	---

Doro Secure 580IUP



Ringer volume settings except off 7

Acoustics

Maximum receiving amplification (dB) 35

Headset included ✓

Lanyard included ✓

USB-cable included ✓
