



Integrity® Cleanroom

Integrity® Full Finger Glove Liner 600-0661

White seamless 100% nylon glove liner greatly reduces perspiration and limits skin irritation caused by contact with glove material such as latex, PVC and also other chemical handling gloves.

It's sturdy construction allows liners to be laundered and reused.

FEATURES

- Durable and comfortable
- Reusable, ambidextrous, seamless construction
- Color coded cuffs denotes size

APPLICATIONS

- Suitable for use in controlled environments
- For use in laboratories and manufacturing environments
- Can be used as inspection gloves to prevent fingerprints on circuit boards, lenses, optics and other critical surfaces



PERFORMANCE CHARACTERISTICS

| MATERIAL COMPOSITION | THICKNESS | COLOUR | SURFACE RESISTIVITY |
|----------------------|--------------|------------------------------|---------------------|
| 100% Nylon | 2 mm +/- 10% | White with color coded cuffs | 1x10 ⁹ Ω |

DIMENSIONS

| WIDTH | 8.0 +/- 0.5 cm | 8.5 + 0.5 cm | 9.0 +/- 0.5 cm | 9.5 +/- 0.5cm |
|--------|----------------|----------------|----------------|---------------|
| LENGTH | 21.0 +/- 1.0cm | 22.0 +/- 1.0cm | 23.0 +/- 1.0cm | 24 +/- 1.0cm |

PACKAGING:

- 1pair / pack
- 10 packs / bag
- 100 bags / carton

| | |
|--------------|----------|
| PRODUCT CODE | 600-0661 |
|--------------|----------|

Call +44 (0) 1473 836205 Email info@integritycleanroom.com [/integrity_eu](https://twitter.com/integrity_eu) [/company/integrity-cleanroom](https://www.linkedin.com/company/integrity-cleanroom)

IMPORTANT NOTICE: This data sheet and its contents (the "Information") belong to the Integrity or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Integrity assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Integrity was aware of the possibility of such loss or damage arising) is excluded. © Integrity.

