

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [33472-0601](#)  
**Status:** **Active**  
**Overview:** [MX150™ Sealed and Unsealed Connector System](#)  
**Description:** MX150™ Sealed Female Connector, Dual Row, 6 Circuits, Polarization A, without Connector Position Assurance, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-33472-100 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-33611-001 (PDF)</a>
<a href="#">Product Specification PS-33472-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**General**

Product Family	Crimp Housings
Series	<a href="#">33472</a>
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	<a href="http://ewcap.uscarteams.org">http://ewcap.uscarteams.org</a>
Overview	<a href="#">MX150™ Sealed and Unsealed Connector System</a>
Product Name	MX150™
UPC	800756537443

**Physical**

Circuits (maximum)	6
Circuits Detail	6
Color - Resin	Black, Natural
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	9.430/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

**Electrical**

Current - Maximum per Contact	22.0A
-------------------------------	-------

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-33472-100, AS-33611-001
Product Specification	PS-33472-000
Sales Drawing	150-S-006-2-Z02, SD-33472-0001, SD-33472-0002, SD-33472-061

<b>EU RoHS</b> <b>ELV and RoHS</b> <b>Compliant</b> <b>REACH SVHC</b> <b>Contains SVHC: No</b> <b>Low-Halogen Status</b> <b>Low-Halogen</b>	<b>China RoHS</b> 
---	--

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[33472Series](#)

**Mates With**

[33482](#) Male Dual Row Sealed Connector

**Use With**

[33012](#) MX150™ Female Terminal,  
[34345-0001](#) MX150™ Cavity Plug Sealed