


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **50372-8100**  
**Status:** **Active**  
**Overview:** DuraClik™ Connector System  
**Description:** DuraClik™ Crimp Terminal, Female, 22-26 AWG, Bag

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-51225-003 (PDF)</a>
<a href="#">Product Specification PS-51089-001 (PDF)</a>	<a href="#">Product Specification PS-52968-006 (PDF)</a>
<a href="#">Product Specification PS-51089-005 (PDF)</a>	<a href="#">Product Specification PS-52968-007 (PDF)</a>
<a href="#">Product Specification PS-51090-004 (PDF)</a>	<a href="#">Product Specification PS-53717-002 (PDF)</a>
<a href="#">Product Specification PS-51090-005 (PDF)</a>	<a href="#">Product Specification PS-54111-002 (PDF)</a>
<a href="#">Product Specification PS-51090-009 (PDF)</a>	<a href="#">Product Specification PS-54214-001 (PDF)</a>
<a href="#">Product Specification PS-51090-016 (PDF)</a>	<a href="#">Product Specification PS-54452-007 (PDF)</a>
<a href="#">Product Specification PS-51090-017 (PDF)</a>	<a href="#">Product Specification PS-55533-004 (PDF)</a>
<a href="#">Product Specification PS-51160-001 (PDF)</a>	<a href="#">Packaging Specification SPK-50372-001 (PDF)</a>
<a href="#">Product Specification PS-51160-006 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**General**

Product Family	Crimp Terminals
Series	50372
Application	Signal
Crimp Quality Equipment	Yes
Overview	<u>DuraClik™ Connector System</u>
Product Name	DuraClik™
UPC	800753352704

**Physical**

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	26.800/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40mm max.
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	3.0A
Voltage - Maximum	125V

**Material Info**

**Reference - Drawing Numbers**

Crimp Specification	CS-50372-001
Packaging Specification	SPK-50372-001
Product Specification	PS-51089-001, PS-51089-005, PS-51090-004, PS-51090-005, PS-51090-009, PS-51090-016, PS-51090-017, PS-51160-001, PS-51160-006, PS-51225-003, PS-52968-006, PS-52968-007, PS-53717-002, PS-54111-002, PS-54214-001, PS-54452-007, PS-55533-004, RPS-51065-032, RPS-51089-002, RPS-51089-006, RPS-51090-001, RPS-51090-006, RPS-51090-008, RPS-51090-010,

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC**  
**Contains SVHC: No**  
**Low-Halogen Status**  
**Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

50372Series

**Use With**

502351 DuraClik™ Wire-to-Board Receptacle Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
-------------	-----------

Extraction Tool	<a href="#">0011030043</a>
-----------------	----------------------------

Hand Crimp Tool	<a href="#">0638235100</a>
-----------------	----------------------------

for 2.00mm Pitch

Wire-to-Board Crimp

Terminal

**Japan**

Description	Product #
-------------	-----------

Hand Crimper	<a href="#">0571755000</a>
--------------	----------------------------

Extraction Tool	<a href="#">0573216000</a>
-----------------	----------------------------

Sales Drawing

RPS-51090-012, RPS-51090-013, RPS-51090-014,  
RPS-51090-015, RPS-51090-017, RPS-51090-018,  
RPS-51090-021, RPS-51090-022, RPS-51090-026,  
RPS-51160-003, RPS-51160-005, RPS-51339-004,  
RPS-51339-007, RPS-52968-005, RPS-52968-012,  
RPS-52968-013, RPS-52969-004, RPS-52969-006,  
RPS-53324-001, RPS-54111-004, RPS-54111-005,  
RPS-54269-004, RPS-87369-001  
SD-50372-001, SD-50372-8\*00

This document was generated on 04/17/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**