


HDMI over Dual Cat5/Cat6 Extender Wall Plate Kit with Transmitter and Receiver

MODEL NUMBER: **P167-000**



Description

Tripp Lite's HDMI Over Dual Cat5 Extender Wallplate Kit is the perfect solution for those who need to extend a HDMI signal over a long distance over two Cat5/6 cables.

- When using 24Awg, Solid Wire Cat6 cable, a 1080p (24Hz) or 1080i (60Hz) signal can be extended up to 150 ft. from the source.
- When using 24Awg, Solid Wire Cat6 cable, a 3D signal can be extended up to 100 ft.
- When using 24Awg, Solid Wire Cat5 cable, a 1080p (24Hz) or 1080i (60Hz) signal can be extended up to 100 ft. from the source.
- When using 24Awg, Solid Wire Cat5 cable, a 3D signal can be extended up to 50 ft.

Simply run two Cat5/6 cables between the local transmitter and remote receiver wallplates, and plug in standard Tripp Lite HDMI cables to the HDMI source and the display. The Green LED on the remote receiver wallplate lets you know that power from the source and monitor. When functioning properly, only the Green LED will be lit. If the Red LED is illuminated, it means that the remote receiver is not receiving a functional signal from the source.

The P167-000 comes with both local transmitter and remote receiver wallplates. DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio are supported, and it is compliant with HDCP, EDID and DDC. 24-bit True Color (8-bits per channel) is supported. No external power is required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Extends a 1080p (24Hz) or 1080i (60Hz) signal up to 150 ft. using 24Awg, Solid Wire Cat6* cabling (Tripp Lite N222-Series, or N224-Series)
- Extends a 1080p (24Hz) or 1080i (60Hz) signal up to 100 ft. using 24Awg, Solid Wire Cat5 cabling
- Extends a 3D signal up to 100 ft. using 24Awg, Solid Wire Cat6 cabling, or up to 50 ft. using 24Awg, Solid Wire Cat5 cabling
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Supports HDCP, EDID and DDC

Highlights

- Extends a 1080p (24Hz) or 1080i (60Hz) signal up to 150 ft. using 24Awg, Solid Wire Cat6* cabling (Tripp Lite N222-Series, or N224-Series)
- Extends a 3D signal up to 100 ft. using 24Awg, Solid Wire Cat6 cabling
- Supports 24-bit True Color (8-bits per channel)
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Supports HDCP, EDID and DDC
- No external power required

*When using Cat5 cable, the maximum extension distance is reduced by 50 ft.

Applications

- Home or Business theater installations where the HDMI display is more than 5 meters from the source

Package Includes

- Local Transmitter and Remote Receiver Wallplates
- 110 Punchdown Tool
- (x4) Wallplate Screws
- Owner's Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Supports 24-bit True Color (8-bits per channel)
- No external power required
- Use Tripp Lite P568-Series HDMI cables from wallplates to devices
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

PRODUCT OVERVIEW	
Product Overview	HDMI Over Cat5/6 Wallplate Extender Kit
CONNECTIONS	
Connector A	HDMI (FEMALE)
Connector B	HDMI (FEMALE)
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>