

In most applications, a signal booster (Model Number: B122-000-60) should be used with this cable to ensure a signal strong enough for your display. An alternate solution is to use a Tripp Lite HDMI over Cat5 Extender (Model Number: B126-1A1) in place of a 50 ft. HDMI cable and signal booster.

## High Speed HDMI Plenum Rated Cable, Ultra HD 4K x 2K, Digital Video with Audio (M/M), 50-ft.

MODEL NUMBER: **P568-050-P**



### Description

Tripp Lite's 50-ft. High Speed HDMI (High-Definition Multimedia Interface) Plenum-rated Gold Cable allows interconnection between digital display devices, such as DTV's (Digital Television), Plasma displays, LCD TV's and projectors, to Digital source devices, such as Digital Set-Top boxes, Blu-Ray players and AV receivers. Use Plenum-rated cables where local codes call for a fire resistant cable, such as schools, commercial buildings, etc. Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter. HDMI assures that the best audio/video signal is always sent from the source (HDTV signal, Blu-Ray Player) to the display (Projection Television, LCD, Plasma, etc.). It does this by allowing uncompressed video and multi-channel audio data to be input to the display device through a single cable. An HDMI connection allows input at high rates of speed, up to 10.2 Gbps. In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display

### Features

- Plenum-rated for use where local code calls for a fire resistant cable
- Creates a pure digital connection between HDMI-enabled HDTV display devices and HDMI-enabled digital video sources
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- Gold-plated connectors provide optimal signal transfer
- Premium double-shielded cable protects against outside noise (EMI/RFI)
- Impedance-matched twisted-pair construction reduces cross-talk and interference
- Bandwidth up to 10.2 Gbps - Full 1080p resolution
- In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display
- Supports Ultra High Definition (UHD) 4Kx2K video resolutions up to 3840 x 2160

## Specifications

### Highlights

- Plenum-rated for use where local code calls for a fire resistant cable
- Premium double-shielded digital audio/video cable
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- Gold-plated connectors provide optimal signal transfer
- Bandwidth up to 10.2 Gbps - Full 1080p resolution
- High Speed HDMI and HDCP compliant
- Supports Ultra High Definition (UHD) 4Kx2K video resolutions up to 3840 x 2160

### Package Includes

- High Speed HDMI Plenum Rated Cable, Ultra HD 4K x 2K, Digital Video with Audio (M/M), 50-ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.triplite.com

<b>OVERVIEW</b>	
Cable Type	HDMI
<b>INPUT</b>	
Cable Length (ft.)	50
Cable Length (m)	15.24
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	HDMI (MALE)
Connector B	HDMI (MALE)
Number of Connectors	2
<b>SPECIAL FEATURES</b>	
Chromebook Compatible	Yes
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.triplite.com/products/product-certification-agencies>