

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0002081201](#)  
**Status:** **Active**  
**Overview:** [Disk Drive Power Connector](#)  
**Description:** [Disk Drive Power Connection System, Female Crimp Terminal, Reel, Phosphor Bronze, AWG 14-20](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-8981-4M\\*/4P\\* \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">8980</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Disk Drive Power Connector</a>
Product Name	Disk Drive Power
UPC	800753615939

**Physical**


Durability (mating cycles max)	50
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.223/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.03-2.74mm
Wire Size AWG	14, 16, 18, 20
Wire Size mm <sup>2</sup>	N/A

**Material Info**

Old Part Number	8980-3C
-----------------	---------

**Reference - Drawing Numbers**

Product Specification	PS-8981-4M*/4P*
Sales Drawing	SD-8980-3*



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contains SVHC(2014 December 17): No

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[8980](#) Series

**Use With**

15-24-4048

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">0638117000</a>
Mini-Mac™	<a href="#">0638929000</a>
Applicator for Disk Drive Power Connector System, Female 14-20 AWG	
Extraction Tool	<a href="#">0011030037</a>
Terminator Die	<a href="#">0011402282</a>

**Japan**

**Description**

**Product #**

Applicator for M211A 0571023000

Bench Press, 14-22

AWG Wire

This document was generated on 07/07/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**