

## 40Gb Pass-Through Cassette - (x6) 12-Fiber MTP/MPO

MODEL NUMBER: **N482-6M12-6M12**



### Description

Tripp Lite's N482-6M12-6M12 is a High Density 40Gb Pass-through Cassette, with (x6) 12-Fiber MTP/MPO connections. For use with Tripp Lite's N482-01U and N482-02U High Density Fiber Enclosure Panels; up to 5 cassettes per N482-01U, or up to 14 cassettes per N482-02U. Installation is simple, with the cassette being easily installed or removed using push / pull tabs to lock or unlock it from the panel; no tools required. Furthermore, each cassette features factory terminated connectors that reduce the time and labor required of field connector terminations. Constructed of heavy-duty steel housing.

### Features

- High Density Fiber Cassette for use with Tripp Lite N482-01U and N482-02U High Density Fiber Enclosure Panels
- 40Gb Pass-through Cassette, with (x6) 12-Fiber MTP/MPO connections
- Installation is simple, with the cassette being easily installed or removed using push / pull tabs to lock or unlock it from the panel; no tools required.
- Factory terminated connectors reduce the time and labor required of field connector terminations
- Constructed of heavy-duty steel housing

## Specifications

OVERVIEW	
Cable Type	Fiber
PHYSICAL	
Unit Dimensions (hwd / in.)	1.2 x 3.5 x 0.9
Unit Dimensions (hwd / cm)	3.05 x 8.89 x 2.29
Unit Weight (lbs.)	0.18

### Highlights

- High Density Fiber Cassette for use with Tripp Lite N482-01U and N482-02U High Density Fiber Enclosure Panels
- 40Gb Pass-through Cassette, with (x6) 12-Fiber MTP/MPO connections
- Factory terminated connectors reduce the time and labor required of field connector terminations

### Applications

High density network applications as specified in the Data Center Cabling Standard TIA 942 for cross connects in main distribution, horizontal distribution, and equipment distribution areas

### Package Includes

- N482-6M12-6M12 40Gb Pass-through Cassette - (x6) 12-Fiber MTP/MPO
- Quick Start Guide



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Unit Weight (kg)	0.08
Color	Black
<b>CONNECTIONS</b>	
Connector A	HARDWIRE
Connector B	HARDWIRE
Ports	6
Side A - Connector 1	12-FIBER, MTP/MPO (FEMALE) (X6)
Side B - Connector 1	12-FIBER, MTP/MPO (FEMALE) (X6)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>