

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0330013004

Status:

Active

Overview:

MX150™ Sealed and Unsealed Connector System

Description:

MX150™ Female Terminal Sealed, Gold Plating, 16, 18 and 20 AWG, Left Reel Payoff

Documents:

Drawing (PDF)

Product Specification PS-33012-002 (PDF)

Application Specification AS-33012-002 (PDF)

Test Summary TS-33001-002 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

Crimp Quality Equipment

MolexKits

Overview

Product Name

UPC

Crimp Terminals

33001

Power

Left Reel Payoff, Small Polarization Rib

Yes

Yes

MX150™ Sealed and Unsealed Connector System

MX150™

822350084178

Physical

Gender

Grip Code

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Female

18

High Performance Alloy (HPA)

Gold

Unplated

0.435/g

Reel

0.762µm

2.540µm

Crimp or Compression

2.60mm max.

18, 20

0.75 - 1.00

Electrical

Current - Maximum per Contact

Voltage - Maximum

22.0A

250V

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Application Specification

Product Specification

Sales Drawing

Test Summary

AS-33012-002

PS-33012-002

SD-33012-002

TS-33001-002



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Relevant

ELV

Compliant

Search Parts in this Series

33001 Series

Use With

33472 Dual Row Housing. 33476 Hybrid Housing. 33471 Single Row Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hand Crimp Tool, 18-22AWG

0638116000

Hand Crimp Tool, Metric 1.00 and 1.50

0638116100

Hand Crimp Tool

0638116200

Metric 0.5 and 0.75

FineAdjust™	<u>0639000800</u>
Applicator for MX150	
Receptacle, 18 AWG	
Wire	
FineAdjust™	<u>0639000900</u>
Applicator for MX150	
Receptacle, 20 AWG	
Wire	
Manual Extraction	<u>0638131500</u>
Tool	

This document was generated on 06/30/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION