

Mini Displayport to VGA/DVI/HDMI All-in-One Adapter/Converter, 6-in.

MODEL NUMBER: **P137-06N-HDV**



Description

Tripp Lite's P137-06N-HDV allows you to convert your computer's Mini DisplayPort (Thunderbolt) to a VGA, DVI, or HDMI monitor as an all-in-one, compact adapter. This passive, plug-and-play adapter requires no external power, drivers, or software, and supports video resolutions up to 1920 x 1200, or HD video resolutions up to 1920 x 1080 (1080p). Compatible with the Thunderbolt port on MAC computers such as MacBook Pro and MacBook Air. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Connect a VGA, DVI, or HDMI monitor to a Mini DisplayPort on your laptop or tablet
- All-in-One converter offers maximum flexibility to connect to any available monitor
- Portable design with built-in cable is perfect for travel and stowing in your laptop bag
- Supports computer video resolutions up to 1920 x 1200 or HD video resolutions up to 1920 x 1080 (1080p)
- Supports up to 36-bit Deep Color (12 bits per channel)
- Compatible with the Thunderbolt port on Mac® computers such as the MacBook Pro and MacBook Air
- Passive converter requires no external power supply
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Connect a VGA, DVI, or HDMI monitor to a Mini DisplayPort on your laptop or tablet
- All-in-One converter offers maximum flexibility to connect to any available monitor
- Plug and Play
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Computer or tablet with a Mini DisplayPort
- Monitor with a VGA, DVI, or HDMI port

Package Includes

- 6 Inch Mini Displayport to VGA / DVI / HDMI All-in-One Adapter / Converter

Specifications

OVERVIEW	
Display Style	Adapter
Cable Type	DisplayPort



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	MINI DISPLAYPORT (MALE)
Connector B	DVI-I (FEMALE)
Connector C	HDMI (FEMALE)
Connector D	HD15 (FEMALE)
SPECIAL FEATURES	
Chromebook Compatible	No
CERTIFICATIONS	
Certifications	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<http://www.tripplite.com/products/product-certification-agencies>