

## Mini DisplayPort to VGA Adapter, Video Converter for Mac/PC, 1920x1200/1080p (M/F), 6-in.

MODEL NUMBER: **P137-06N-VGA**



### Description

Tripp Lite's P137-06N-VGA Mini-Displayport to VGA Adapter allows you to connect a Mac or PC with a Mini-Displayport output to a VGA monitor. Compatible with the Thunderbolt port on Mac computers. Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Fully-molded ends ensure long life enjoyment. It features a simple plug and play design with an integrated chip that converts the digital Mini-Displayport signal to analog VGA; no drivers or setup needed. Simply plug the adapter into your Mini-Displayport source and connect your VGA cable between it and your monitor.

### Features

- Connect a VGA monitor to a Mac or PC with a Mini Displayport output
- Compatible with the Thunderbolt port on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p

## Specifications

OVERVIEW	
Display Style	Adapter
Cable Type	DisplayPort
INPUT	
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6

### Highlights

- Connect a VGA monitor to a Mac or PC with a Mini Displayport output
- Compatible with the Thunderbolt port on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p

### System Requirements

- Mac or PC with a Mini Displayport port; Compatible with the Thunderbolt port on Mac computers
- Monitor with a VGA port

### Package Includes

- Mini-DisplayPort to VGA Adapter



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

PHYSICAL	
Color	White
CONNECTIONS	
Connector A	MINI DISPLAYPORT (MALE)
Connector B	HD15 (FEMALE) & 3.5MM (FEMALE)
SPECIAL FEATURES	
Chromebook Compatible	No
CERTIFICATIONS	
Certifications	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>