

## USB 2.0 Hi-Speed Extension Cable (A M/F) 16-ft.

MODEL NUMBER: **U024-016**



### Description

This 16-ft USB gold extension cable is manufactured using USB2.0 cable. It is designed specifically for use with USB 2.0 A/B device cables. This cable is backwards compatible and can also be used with the older USB 1.1 cables. Made with superior foil shielding for reliable error-free data communications. Features gold plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) makes it perfect for multimedia applications.

### Features

- Supports faster data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil feature twisted 28/24 AWG data lines
- Gold plated connectors provide superior conductivity
- Extend distances of the fast USB 2.0 with this extension cable

### Highlights

- Extend distances of USB 2.0 cables with this extension cable
- Supports faster data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices, especially multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/24 AWG data lines
- Gold plated connectors provide superior conductivity

### System Requirements

- Any device requiring a longer USB cable

### Package Includes

- 16-ft USB 2.0 Gold Extension Cable (USB A M/F)

## Specifications

OVERVIEW	
Cable Type	USB
OUTPUT	
USB Charging	No
INPUT	
Cable Length (ft.)	16
Cable Length (m)	4.88



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	USB A (MALE)
Connector B	USB A (FEMALE)
<b>SPECIAL FEATURES</b>	
Chromebook Compatible	Yes
<b>CERTIFICATIONS</b>	
Certifications	RoHS-Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>