


USB 3.0 SuperSpeed to DisplayPort Dual Monitor External Video Graphics Card Adapter, 512 MB SDRAM - 2560x1600,1080p

MODEL NUMBER: U344-001-DP



Description

Tripp Lite U344-001-DP USB 3.0 to DisplayPort® Multi Monitor External Video Adapter creates an external DisplayPort video card via an available USB 3.0 port on your PC or Laptop. Connect up to six DisplayPort enabled monitors, with support for video resolutions up to 2560x1600, and 5.1 surround sound audio.

Taking advantage of the SuperSpeed USB 3.0 interface (5Gbps), the adapter delivers smooth, high-definition content to your DisplayPort-capable display, and can be used to clone the image on multiple displays, or extended across them. Windows and Intel Mac compatible.

Features

- Adds an additional monitor, LCD or projector through a single USB 3.0 port
- USB 3.0 is 10 times faster than USB 2.0, with transfer rates up to 5 Gbps
- Backward compatible with USB 2.0
- Simultaneously connect up to 6 display adapters
- Automatically resumes from hibernation and suspend modes
- Features 512MB DDR2 SDRAM of memory
- Supports video resolutions up to 2560 x 1600 @ 60Hz
- Video streaming is supported up to 1080p
- Set additional monitors to extend the primary display, duplicate the primary display, or set an additional monitor as the primary display
- Compatible with Windows XP, Vista, 7, 8, and 8.1. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8 and 8.1
- Compatible with Intel Mac OS X 10.8 (10.8.3 and later), 10.9 and 10.10 (Mac OS X 10.9 and 10.10 is limited to a single add-on monitor. See driver Release Notes for details) Supports both 32- and 64-bit.
- Mac OS X versions 10.8.5 and earlier do not support audio over USB 3.0. Mac OS X versions 10.7.x and

Highlights

- Add an additional DisplayPort monitor through a single USB 3.0 port
- Windows and Intel Mac compatible
- Up to six adapters can be added to one computer
- Features 512MB DDR2 SDRAM of memory
- Supports video resolutions up to 2560 x 1600 @ 60Hz

Applications

Office workstation

- View large spreadsheets across multiple screens
- Multitask more effectively without overlapping windows
- Edit on one screen while surfing the Internet for information on the other

On the road

- Do multiple screen presentations without bringing another computer
- Easily provide multiple screen exhibitions in a trade show

Graphics workstation

- Use second display for palettes/tools
- Get a panoramic view of large documents

Editing workstation

- Type documents on one screen while viewing reference material on the other
- Compare two documents simultaneously across two screens



earlier do not support USB 3.0.

- Uses DisplayLink DL3500 chipset

Specifications

OVERVIEW	
Display Style	Adapter
Cable Type	USB
OUTPUT	
Output Amp Capacity	0.34
PHYSICAL	
Unit Dimensions (hwd / in.)	0.4 x 1.0 x 3.2
Unit Dimensions (hwd / cm)	1.016 x 2.54 x 8.13
Unit Weight (lbs.)	0.7
Unit Weight (kg)	0.32
Color	Black
ENVIRONMENTAL	
Storage Temperature Range	-10 to 80 C (14 - 176 F)
Relative Humidity	Less than 85%, Non-Condensing
Operating Temperature	10 - 40 C (50 - 104 F)
CONNECTIONS	
Connector A	USB 3.0 A (MALE)
Connector B	DISPLAYPORT (FEMALE)
SPECIAL FEATURES	
Chromebook Compatible	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

Financial analysis

- Have one monitor per data stream
- View charts and live data at the same time

Entertainment

- View videos/TV on one screen and reviews on the other
- Get additional perspectives when playing games

System Requirements

- Compatible with Windows XP, Vista, 7, 8, and 8.1. Supports both 32- and 64-bit.
- Supports Surface tablets running non-RT Windows 8 and 8.1
- Compatible with Intel Mac OS X 10.8 (10.8.3 and later), 10.9 and 10.10 (Mac OS X 10.9 and 10.10 is limited to a single add-on monitor. See Release Notes for details) Supports both 32- and 64-bit.
- Mac OS X versions 10.8.5 and earlier do not support audio over USB 3.0. Mac OS X versions 10.7.x and earlier do not support USB 3.0.
- Reference the owner's manual for system requirements when using multiple adapters or when using the add-on monitor for DVD playback.

Package Includes

- U344-001-DP Adapter
- Driver CD
- USB 3.0 Cable
- Owners Manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<http://www.tripplite.com/products/product-certification-agencies>