

Universal Reversible USB 2.0 Hi-Speed Converter Adapter Cable (Reversible A to 5Pin Mini B M/M), 1-ft.

MODEL NUMBER: UR030-001



Description

Tripp Lite's UR030-001, 1-ft, USB 2.0 Universal / Reversible "A" to Mini-B 5-pin device cable, meets or exceeds USB 2.0 Specifications. Connects a Digital camera, PDA, Cell Phone, etc to a USB port on a computer or hub. Backward compatible - can be used with older USB1.1 applications as well. All Tripp Lite USB 2.0 cabling include superior foil shielding for reliable, error-free data communications. Features nickel plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- Universal / Reversible "A" connector plugs in any direction
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, Cell Phones, PDA's, etc with 5-Pin Mini-B USB connectors
- Supports faster data transfer rate (1.5 to 480 Mbps) for low speed and high speed devices including multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum Mylar foil
- Nickel plated connectors and gold plated copper contacts for superior conductivity.
- Molded connectors and integral strain relief for extra durability and long life.

Specifications

OVERVIEW	
Cable Type	USB
OUTPUT	
USB Charging	No

Highlights

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Meets or Exceeds USB 2.0 Specifications
- Connects to Cameras, PDA's, etc with Mini-B 5-Pin connectors

System Requirements

- Any USB device requiring a USB cable with Mini-B 5-Pin connector
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

- 1-ft. USB2.0 Universal / Reversible A to Mini-B Device Cable (A Male to 5Pin Mini-B Male)



INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
CONNECTIONS	
Connector A	REVERSIBLE USB A (MALE)
Connector B	USB MINI-B 5-PIN (MALE)
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.triplite.com/products/product-certification-agencies>