

7-Port Rugged Industrial USB 2.0 Hi-Speed Hub w 15KV ESD Immunity and metal case, Mountable

MODEL NUMBER: **U223-007-IND**



Description

Tripp Lite's U223-007-IND is a rugged, all metal constructed USB 7-Port hub for use in data centers, work areas, and Industrial applications. Can be mounted on a wall or din-rail with included mounting hardware. Supports Hi-Speed USB 2.0 transfer rates at 480mbps, but is also backward compatible to USB 1.1 (12mbps). Hub is bus-powered through the computer connection, or can self power with an external adapter (not included) or via the included 3-wire terminal block connector (9-36V).

Features

- Industrial-grade, rugged all metal 7-port USB hub
- Supports USB 1.1 and 2.0 transfer speeds (12 - 480mbps)
- Wall or Din Rail mountable - hardware included
- Bus Powered or optional 3-Wire DC Terminal Block
- Over-current detection and protection circuit design
- ESD protected to $\pm 15kV$
- Automatic link and speed detection
- Plug-and-Play; no software or drivers
- Compatible with all major operating systems

Specifications

OVERVIEW	
Over Current Protection	Yes
Cable Type	USB

Highlights

- Industrial-grade, rugged metal enclosure
- ESD Protected to $\pm 15 kV$
- USB 2.0 Compliant - 480Mbps
- Compatible with all major operating systems

Applications

- Use in areas where hub needs to be securely fastened to a surface, such as din rail or wall
- Use in locations where environment is extreme or possible damage could occur

System Requirements

- Compatible with all major operating systems

Package Includes

- U223-007-IND Hub
- 6ft USB cable x 1
- 3-pin power terminal block
- DIN rail mounting hardware
- Wallmount hardware



OUTPUT	
USB Charging	No
PHYSICAL	
Unit Dimensions (hwd / in.)	1 x 2.5 x 5.6
Unit Dimensions (hwd / cm)	2.5 x 6.4 x 14.2
Material of Construction	Metal
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Relative Humidity	5 to 95% RH
Operating Temperature	0C to 60C (32F to 140F)
CONNECTIONS	
Connector A	USB A (MALE)
Connector B	USB A (FEMALE) (X7)
Number of Connectors	8
Ports	7
SPECIAL FEATURES	
Chromebook Compatible	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>