

#### Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

# Universal Reversible USB 2.0 Hi-Speed Cable (Reversible A to Up-Angle 5Pin Micro B M/M), 6-ft.

### MODEL NUMBER: UR050-006-UPB



#### Description

Tripp Lite UR050-006-UPB, 6-ft. USB 2.0 A to Up-Angle Micro-B cable, features a Universal / Reversible "A" connector, which takes the guesswork out of which way to position the "A" connector for plugging. Furthermore, the Up-Angle Micro B connector is ideal for situations where space is at a premium, and reduces stress / excessive bending on the cable. Micro-USB is the next generation of USB connector that will be found on Cell Phones, PDA's, USB On-the-Go (OTG) devices, Digital Cameras, and more. Smaller and more durable (

10,000 insertion cycles ) than the existing mini-B connectors, the Micro-USB will also handle Power transfers, as well as Data. The USB Implementers Forum ( USB-IF) has designed the Micro-USB to eliminate many of the proprietary Mini connectors found on different manufacturers digital devices, and it will be the standard USB connection on phones from the major cell phone manufacturers. USB 2.0 rated cable handles 480Mbps data transfer rates.

#### Features

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Up-Angle Micro B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Available in lengths up to 10-ft.
- 480Mbps USB 2.0 Data Transfer Rates
- Data and Power transference

## Specifications

OVERVIEW	
Cable Type	USB
OUTPUT	
USB Charging	No

#### Highlights

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Up-Angle Micro B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Next Generation USB Digital Device Connector
- Provides both Data and Power transfers
- USB 2.0 480Mbps Transfer rates

#### **System Requirements**

Digital devices that use the USB
Micro-B Female socket

#### Package Includes

 6-ft. USB2.0 Universal / Reversible A to Up-Angle Micro-USB B Device Cable (A Male to Micro-B Male)



INPUT		
Cable Length (ft.)	6	
Cable Length (m)	1.83	
PHYSICAL		
Color	Black	
ENVIRONMENTAL		
Operating Temperature Range	-10/+75° C (14 to 167° F)	
Storage Temperature Range	-20/+80° C (-4 to 176° F)	
CONNECTIONS		
Connector A	REVERSIBLE USB A (MALE)	
Connector B	MICRO-USB B (MALE)	
SPECIAL FEATURES		
Chromebook Compatible	Yes	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: http://www.tripplite.com/products/product-certification-agencies