

Shelves

= In stock products


Our extensive range of shelves includes various component sizes to complete your workstation. The deepest shelves should be installed at the top, to prevent blocking the work surface. Adjustable shelves and extendable shelves enable more ergonomic and efficient ways of working. The shelves are available in

all module sizes. Steel shelves with lip can be attached at a 0° or 20° angle, and adjustable shelves can be tilted continuously from 0° to 25°. Equipment shelves offer continuous space for storage and equipment. Bookend brackets and lip edges are available options for equipment shelf.

Steel shelf w/lip



Adjustable shelf



Front justified adjustable shelves available on page 84.

Steplessly adjustable shelf



Front justified adjustable shelves available on page 84.

Extendable shelf



Steel equipment shelf



(TLA™) works with TL Advantage™ frames

Packaging top shelf



Shelves M20

name	module	size W x D inches	max Lbs	ESD order No	non-ESD order No
Steel shelf w/lip, 0° or 20° angle	M20	19.29 x 11.81	110	860804-35	
Steel shelf w/lip, 0° or 20° angle	M20	19.29 x 15.74	110	860805-35	
Adjustable shelf, tilt 0° or 25°	M20	18.50 x 19.88	220	92035001	92041001
Adjustable shelf, tilt 0° or 25°	M20	18.50 x 25.59	220	92035002	92041002
Adjustable shelf, stepless depth adj, tilt 0° or 25°	M20	18.50 x 19.88	110	92035003	92041003
Adjustable shelf, stepless depth adj, tilt 0° or 25°	M20	18.50 x 25.59	110	92035004	92041004

Shelves M30

Steel shelf w/lip, 0° or 20° tilt	M30	28.34 x 11.81	110	836028-35	
Steel shelf w/lip, 0° or 20° tilt	M30	28.34 x 15.74	110	852770-35	
Steel Equipment Shelf	M30	28.34 x 11.81	176	E816757-35	
Steel Equipment Shelf	M30	28.34 x 15.74	176	E816758-35	
Equipment Shelf Lip	M30	28.34 x 2		14-94035339	
Adjustable shelf, tilt 0° or 25°	M30	28.34 x 19.88	220	92035005	92041005
Adjustable shelf, tilt 0° or 25°	M30	28.34 x 25.59	220	92035006	92041006
Adjustable shelf, stepless depth adj, tilt 0° or 25°	M30	28.34 x 19.88	110	92035007	92041007
Adjustable shelf, stepless depth adj, tilt 0° or 25°	M30	28.34 x 25.59	110	92035008	92041008
Extendable shelf	M30	28.34 x 15.35	66	92535002	
Chem Shelf	M30	28.34 x 4.5	33	14-94235610	

Shelves M36

Steel shelf w/lip, 0° or 20° tilt	M36	34.25 x 11.81	110	852283-35	
Steel shelf w/lip, 0° or 20° tilt	M36	34.25 x 15.74	110	852769-35	
Steel Equipment Shelf	M36	34.25 x 11.81	176	E816759-35	
Steel Equipment Shelf	M36	34.25 x 15.74	176	E816760-35	
Equipment Shelf Lip	M36	34.25 x 2		14-9403556	
Adjustable shelf, tilt 0° or 25°	M36	34.25 x 19.88	220	92035009	92041009
Adjustable shelf, tilt 0° or 25°	M36	34.25 x 25.59	220	92035010	92041010
Adjustable shelf, stepless depth adj, tilt 0° or 25°	M36	34.25 x 19.88	110	92035011	92041011
Adjustable shelf, stepless depth adj, tilt 0° or 25°	M36	34.25 x 25.59	110	92035012	92041012
Extendable shelf	M36	34.25 x 15.35	66	92535003	
Chem Shelf	M36	34.25 x 4.5	33	14-94035973	

Shelves M48

Steel equipment shelf	M48	45.94 x 11.81	176	854480-35	
Steel equipment shelf	M48	45.94 x 15.74	176	854483-35	
Equipment Shelf Lip	M48	45.94 x 2		14-9403557	
Chem Shelf	M48	45.94 x 4.5	33	14-94235646	
Packaging shelf, top	M48	45.94 x 15.74	176	E819798-35	

Shelves M53

Steel shelf w/lip, 0° or 20° tilt	M53	52.75 x 11.81	110	860787-35	
Steel shelf w/lip, 0° or 20° tilt	M53	52.75 x 15.74	110	860788-35	
Adjustable shelf, tilt 0° or 25°	M53	51.96 x 19.88	220	92035013	92041013
Adjustable shelf, tilt 0° or 25°	M53	51.96 x 25.59	220	92035014	92041014
Chem shelf	M53	51.96 x 4.5	33	14-94235653	
Packaging shelf, top	M53	51.96 x 15.74	176	859013-35	

Packaging bottom shelf



Chem shelf

