

General Information

Kit Part Number:	76650-0045
Description:	.250" Tab Size Nylon Fully Insulated Quick Disconnect Solderless Terminals, with Universal Crimp Tool
With Tool:	Tool
Application:	Automotive / Transportation, Consumer Products, Industrial Equipment, MRO (Maintenance Repair and Operations)
Connector Family:	Solderless Terminals
Solution:	Maintenance, Repair and Operation Connectors
Connector Type:	Solderless Terminals
Number of Pieces:	301
RoHS:	Yes

Specifications

Insulation:	Nylon Fully Insulated
Mounting Style:	Non-Mounted
Orientation:	Assorted .250" Tab Quick Disconnect Terminals
Product/Type:	.250" Tab Quick Disconnects
Stud/Tab Size:	.250" Tabs
Tool Included:	Yes
Wire Gauge (AWG):	12-10, 16-14 , 22-18

Product Highlights

Product Highlights

Quick disconnects allow for quickly connecting or disconnecting a terminal. The front end of the terminal has a female-type receptacle which allows the terminal to slide onto and off of a male blade.

Features and Benefits

- Color-coded insulator allows easy identification of terminal size and wire gauge.
- A wire stop stamped into the crimp barrel prevents insertion of over-stripped wires.
- Terminals funnel entrance is designed for increased crimping rates by speeding wire delivery into the crimp section and eliminating wire strand fold back.

Applications

- MRO (Maintenance Repair and Operations)
- Consumer applications
- Power applications
- Motor applications

Bill of Materials

Part No.	Qty In Kit	Description	Datasheet	P/N Details	Search Distributors Inventory
19004-0001	50	Fully Insulated 6.35mm (.250") Male Quick Disconnect Termina...	Datasheet	Details	Search
19004-0005	50	Fully Insulated 6.35mm (.250") Male Quick Disconnect Termina...	Datasheet	Details	Search
19004-0009	50	Fully Insulated 6.35mm (.250") Male Quick Disconnect Termina...	Datasheet	Details	Search
19005-0001	50	Fully Insulated 6.35mm (.250") Female Quick Disconnect Termi...	Datasheet	Details	Search
19005-0010	50	Fully Insulated 6.35mm (.250") Female Quick Disconnect Termi...	Datasheet	Details	Search
CT-4071-1R	1	Universal Hand Crimpping Tool, 22-10 AWG		Details	Search
19005-0005	50	Fully Insulated 6.35mm (.250") Female Quick Disconnect Termi...	Datasheet	Details	Search

Recommended Tool

Part No.	Included in Kit
CT-4071-1R	Yes
64001-0400	No
64001-4700	No
64001-1500	No
64001-4900	No
64001-5100	No
64005-5100	No
64005-4900	No





