

9/125 Single mode Simplex Fiber Assemblies

L-com's 9/125 Single mode simplex fiber optic cables are 100% optically tested and utilize a PC polish. Check **L-com.com** for additional length and connector options. All cable measurements are in meters. 1m=3.28ft. See L-com's Custom Cable Configurator to make your own length variations of existing cables in any whole foot or meter increment.


Item #	Description	1-9
9/125 Single mode Simplex Fiber Patch Cords		
LC, SC and ST configurations shown below; see L-com.com for complete listings.		
SFOLC-01	Single mode Fiber Cable, LC/LC, OFNR Jacket, Yellow, 1.0m	21.65
SFOLC-03	Single mode Fiber Cable, LC/LC, OFNR Jacket, Yellow, 3.0m	22.70
SFOLC-05	Single mode Fiber Cable, LC/LC, OFNR Jacket, Yellow, 5.0m	23.70
SFOSC-01	Single mode Fiber Cable, SC/SC, OFNR Jacket, Yellow, 1.0m	10.50
SFOSC-03	Single mode Fiber Cable, SC/SC, OFNR Jacket, Yellow, 3.0m	11.55
SFOSC-05	Single mode Fiber Cable, SC/SC, OFNR Jacket, Yellow, 5.0m	12.60
SFOST-01	Single mode Fiber Cable, ST/ST, OFNR Jacket, Yellow, 1.0m	10.50
SFOST-03	Single mode Fiber Cable, ST/ST, OFNR Jacket, Yellow, 3.0m	11.55
SFOST-05	Single mode Fiber Cable, ST/ST, OFNR Jacket, Yellow, 5.0m	12.60
SFOSC-LC-01	Single mode Fiber Cable, SC/LC, OFNR Jacket, Yellow, 1.0m	15.45
SFOSC-LC-03	Single mode Fiber Cable, SC/LC, OFNR Jacket, Yellow, 3.0m	16.50
SFOSC-LC-05	Single mode Fiber Cable, SC/LC, OFNR Jacket, Yellow, 5.0m	17.55
SFOST-LC-01	Single mode Fiber Cable, ST/LC, OFNR Jacket, Yellow, 1.0m	15.75
SFOST-LC-03	Single mode Fiber Cable, ST/LC, OFNR Jacket, Yellow, 3.0m	16.80
SFOST-LC-05	Single mode Fiber Cable, ST/LC, OFNR Jacket, Yellow, 5.0m	17.85

9/125 Single mode APC Fiber Assemblies

Looking for Single mode assemblies with APC (Angled Physical Contact) connectors for the lowest possible back reflection? Check them out here. All APC assemblies utilize OFNR (Riser) jackets. See L-com's Custom Cable Configurator to make your own custom lengths.

9/125 Single mode APC Fiber Patch Cords

LC and ST options shown, see **L-com.com** for complete listings including FC connector assemblies



SFOLCA-01	Single mode Fiber APC Cable, LC/LC, OFNR Jacket, Yellow, 1.0m	25.75
SFOLCA-03	Single mode Fiber APC Cable, LC/LC, OFNR Jacket, Yellow, 3.0m	26.80
SFOLCA-05	Single mode Fiber APC Cable, LC/LC, OFNR Jacket, Yellow, 5.0m	27.00
SFODLCA-01	Single mode Fiber APC Cable, Dual LC/Dual LC, OFNR Jacket, Yellow, 1.0m	51.45
SFODLCA-03	Single mode Fiber APC Cable, Dual LC/Dual LC, OFNR Jacket, Yellow, 3.0m	53.55
SFODLCA-05	Single mode Fiber APC Cable, Dual LC/Dual LC, OFNR Jacket, Yellow, 5.0m	55.65
SFOSCA-01	Single mode Fiber APC Cable, SC/SC, OFNR Jacket, Yellow, 1.0m	12.60
SFOSCA-03	Single mode Fiber APC Cable, SC/SC, OFNR Jacket, Yellow, 3.0m	13.65
SFOSCA-05	Single mode Fiber APC Cable, SC/SC, OFNR Jacket, Yellow, 5.0m	14.70
SFODSCA-01	Single mode Fiber APC Cable, Dual SC/Dual SC, OFNR Jacket, Yellow, 1.0m	24.10
SFODSCA-03	Single mode Fiber APC Cable, Dual SC/Dual SC, OFNR Jacket, Yellow, 3.0m	26.25
SFODSCA-05	Single mode Fiber APC Cable, Dual SC/Dual SC, OFNR Jacket, Yellow, 5.0m	27.85

9/125 Single mode APC Couplers

In order to achieve low back reflection values, some fiber assemblies utilize a connector with an APC (Angled Physical Contact) connector. These APC connectors require special couplers that have tight tolerance alignment slots to assure proper orientation of the mated APC connectors. These APC couplers are specifically designed for this application.

Item #	Description	Body	Sleeve	1-9
9/125 Single mode APC Couplers				
FOA-804	Simplex LC/LC APC Coupler Low Profile	Plastic	Ceramic	14.40
FOA-805	Duplex LC/LC APC Coupler Low Profile	Plastic	Ceramic	15.40
FOA-017	Simplex SC/SC APC Coupler with Mounting Flange	Plastic	Ceramic	10.30
FOA-018	Duplex SC/SC APC Coupler with Mounting Flange	Plastic	Ceramic	19.10
FOA-019	Simplex FC/FC APC Coupler with D-Hole Mount	Metal	Ceramic	15.45

MTRJ to MTRJ Fiber Optic Coupler

Use of this coupler requires one of the two mating MTRJ connectors to contain alignment pins.

FOA-600	MTRJ Coupler with Mounting Flange	Plastic	None	4.20
---------	-----------------------------------	---------	------	------

Assorted FC Couplers/Adapters Not Shown Elsewhere

FOA-003	Simplex FC Fiber Coupler with Square Mount	Metal	Bronze	6.85
FOA-003A	Simplex FC Fiber Coupler with Square Mount	Metal	Ceramic	10.00
FOA-013	Simplex FC Fiber Coupler with Rectangular Mount	Metal	Bronze	6.85
FOA-013A	Simplex FC Fiber Coupler with Rectangular Mount	Metal	Ceramic	10.00
FOA-033	Simplex FC Fiber Coupler with D-Hole Mount	Metal	Bronze	6.70
FOA-033A	Simplex FC Fiber Coupler with D-Hole Mount	Metal	Ceramic	9.80
FOA-301	Simplex ST-FC Fiber Adapter with Square Mount	Metal	Bronze	9.75
FOA-311	Simplex ST-FC Fiber Adapter with Rectangular Mount	Metal	Bronze	3.70
FOA-311A	Simplex ST-FC Fiber Adapter with Rectangular Mount	Metal	Ceramic	11.05
FOA-302	Simplex SC-FC Fiber Adapter with Square Mount	Metal	Bronze	9.75

Fiber Optic Bulkhead Coupler Kit - Great for Tool Kits

The FOA-123 Fiber Optic Bulkhead Coupler Kit comes complete with two ST-ST (FOA-001), two SC-SC (FOA-002), one FC-FC (FOA-003) and a handy four compartment carrying case. All couplers are bulkhead mountable.

FOA-123	Fiber Optic Bulkhead Coupler Kit	20.60
---------	----------------------------------	-------

Fiber Optic Coupler/Adapter Kit - Complete Flexibility

This is the most complete kit of fiber adapters and couplers we offer, allowing connections between nearly all like interfaces and adapting from one style interface to another including LC-LC (FOA-500A), MPO-MPO (FOA-012), ST-ST (FOA-001), SC-SC (FOA-002), ST-SC (FOA-201), FC-FC (FOA-003), ST-FC (FOA-301), SC-FC (FOA-302), MTRJ-MTRJ (FOA-600), SMA-SMA (FOA-004), and MU-MU (FOA-701).

FOA-321	Fiber Optic Coupler/Adapter Kit	91.70
---------	---------------------------------	-------

