

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0334720802](#)
Status: **Active**
Overview: [MX150™ Sealed and Unsealed Connector System](#)
Description: MX150™ Sealed Female Connector, Dual Row, 8 Circuits, Polarization B, without Connector Position Assurance, Light Gray

Documents:

| | |
|--|--|
| 3D Model | Application Specification AS-33472-100 (PDF) |
| Drawing (PDF) | Application Specification AS-33611-001 (PDF) |
| Product Specification PS-33472-000 (PDF) | RoHS Certificate of Compliance (PDF) |

General

| | |
|--------------------------------|---|
| Product Family | Crimp Housings |
| Series | 33472 |
| Application | Power, Wire-to-Wire |
| Comments | No Connector Position Assurance (CPA) |
| More Detailed Tech Information | http://ewcap.uscarteams.org |
| Overview | MX150™ Sealed and Unsealed Connector System |
| Product Name | MX150™ |
| UPC | 756054494844 |

Physical

| | |
|-------------------------------|----------------------------|
| Circuits (maximum) | 8 |
| Circuits Detail | 8 |
| Color - Resin | Gray (Light), Natural |
| Gender | Female |
| Glow-Wire Compliant | No |
| Keying to Mating Part | Yes |
| Lock to Mating Part | Yes |
| Material - Resin | Modified Polystyrene Alloy |
| Net Weight | 11.338/g |
| Number of Rows | 2 |
| Packaging Type | Bag |
| Panel Mount | No |
| Pitch - Mating Interface | 3.50mm |
| Polarized to Mating Part | Yes |
| Stackable | No |
| Temperature Range - Operating | -40°C to +125°C |

Electrical

| | |
|-------------------------------|-------|
| Current - Maximum per Contact | 22.0A |
|-------------------------------|-------|

Solder Process Data

| | |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|--|
| Application Specification | AS-33472-100, AS-33611-001 |
| Product Specification | PS-33472-000 |
| Sales Drawing | 150-S-008-2-Z02, SD-33472-0002, SD-33472-081, SD-33472-082 |



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Not Relevant

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Not Relevant

Compliant

Search Parts in this Series

[33472](#) Series

Mates With

[33482](#) Male Dual Row Sealed Connector

Use With

[33012](#) MX150™ Female Terminal,
[34345-0001](#) MX150™ Cavity Plug Sealed