

HAND HELD CASES

Silicone Cover Enclosure

Hand-held Enclosure, suitable for measuring instruments, testing devices, wireless communication devices, medical devices etc.

- Silicone cover accessory available.
- Available in six sizes, with or without moulded battery compartments. (further battery compartment options available upon request)
- Recess to front for keypads, labels
- Removable end panel at one end
- Battery contact supplied
- Available in two colours: off-white & dark grey.

SPECIFICATION

Materials	Lid & base high impact ABS-UL94-V0
Operating temperature	-10°C to +60°C
Standard colours	Off-White & Dark grey
Standard unit includes:	Lid and Base, self-tapping screw
Options	Silicon case in red, yellow, blue and dark grey

TAKACHI



Without Battery Compartment

Dark Grey

SIZE	MANUFACTURER PART NO.	LENGTH	WIDTH	HEIGHT
1	LC115-N-D	115mm	69mm	19.5mm
2	LC115H-N-D	115mm	69mm	28mm
3	LC135-N-D	135mm	76mm	27mm
4	LC135H-N-D	135mm	76mm	35mm
5	LC165-N-D	165mm	80mm	27mm
6	LC165H-N-D	165mm	80mm	35mm

Off-white

SIZE	MANUFACTURER PART NO.	LENGTH	WIDTH	HEIGHT
1	LC115-N-W	115mm	69mm	19.5mm
2	LC115H-N-W	115mm	69mm	28mm
3	LC135-N-W	135mm	76mm	27mm
4	LC135H-N-W	135mm	76mm	35mm
5	LC165-N-W	165mm	80mm	27mm
6	LC165H-N-W	165mm	80mm	35mm

With Battery Compartment

Dark Grey

SIZE	MANUFACTURER PART NO.	LENGTH	WIDTH	HEIGHT	BATTERY COMPARTMENT
1	LC115-F2-D	115mm	69mm	19.5mm	2 x AAA
2	LC115H-M2-D	115mm	69mm	28mm	2 x AA
3	LC135-M2-D	135mm	76mm	27mm	2 x AA
4	LC135H-M2-D	135mm	76mm	35mm	2 x AA
5	LC165-M4-D	165mm	80mm	27mm	4 x AA
6	LC165H-M4-D	165mm	80mm	35mm	4 x AA

Off-white

SIZE	MANUFACTURER PART NO.	LENGTH	WIDTH	HEIGHT	BATTERY COMPARTMENT
1	LC115-F2-W	115mm	69mm	19.5mm	2 x AAA
2	LC115H-M2-W	115mm	69mm	28mm	2 x AA
3	LC135-M2-W	135mm	76mm	27mm	2 x AA
4	LC135H-M2-W	135mm	76mm	35mm	2 x AA
5	LC165-M4-W	165mm	80mm	27mm	4 x AA
6	LC165H-M4-W	165mm	80mm	35mm	4 x AA

Silicone Cover

- Flexible open faced removable silicon rubber cover
- Fits tightly over base, sides and around edges of lid
- Custom colours available from MOQ 500 pcs per order, just provide us with your pantone colour.



Red Boot

SIZE	MANUFACTURER PART NO.	LENGTH	WIDTH	HEIGHT
1	LCSC115-R	120mm	74mm	24mm
2	LCSC115H-R	120mm	74mm	32.5mm
3	LCSC135-R	141mm	81mm	32mm
4	LCSC135H-R	141mm	81mm	40mm
5	LCSC165-R	171mm	85mm	32mm
6	LCSC165H-R	171mm	85mm	40mm



Yellow Boot

SIZE	MANUFACTURER PART NO.	LENGTH	WIDTH	HEIGHT
1	LCSC115-Y	120mm	74mm	24mm
2	LCSC115H-Y	120mm	74mm	32.5mm
3	LCSC135-Y	141mm	81mm	32mm
4	LCSC135H-Y	141mm	81mm	40mm
5	LCSC165-Y	171mm	85mm	32mm
6	LCSC165H-Y	171mm	85mm	40mm



Blue Boot

SIZE	MANUFACTURER PART NO.	LENGTH	WIDTH	HEIGHT
1	LCSC115-B	120mm	74mm	24mm
2	LCSC115H-B	120mm	74mm	32.5mm
3	LCSC135-B	141mm	81mm	32mm
4	LCSC135H-B	141mm	81mm	40mm
5	LCSC165-B	171mm	85mm	32mm
6	LCSC165H-B	171mm	85mm	40mm



Dark Grey Boot

SIZE	MANUFACTURER PART NO.	LENGTH	WIDTH	HEIGHT
1	LCSC115-D	120mm	74mm	24mm
2	LCSC115H-D	120mm	74mm	32.5mm
3	LCSC135-D	141mm	81mm	32mm
4	LCSC135H-D	141mm	81mm	40mm
5	LCSC165-D	171mm	85mm	32mm
6	LCSC165H-D	171mm	85mm	40mm

* Ruggedised boots available on request