

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0522130211**
Status: **Active**
Overview: Mizu-P25™ Miniature Waterproof Connectors
Description: Mizu-P25™ 2.50mm Pitch Waterproof Wire-to-Wire Receptacle Housing, 2 Circuits

Documents:

3D Model	Application Specification AS-52213-001-JP (PDF)
Drawing (PDF)	Packaging Specification PK-52213-001 (PDF)
Product Specification PS-52213-003 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-52213-001 (PDF)	

Agency Certification

TUV	R72090206
UL	E29179

General

Product Family	Crimp Housings
Series	52213
Application	Signal, Wire-to-Wire
Application Tooling Part Link	57171-6000
Application Tooling Part Link	62202-4400
Comments	See Product Specification for maximum current rating by wire AWG
MolexKits	Yes
Overview	Mizu-P25™ Miniature Waterproof Connectors
Product Name	Mizu-P25™ Waterproof, Splash Proof
UPC	800754376945

Physical

Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	451.300/mg
Number of Rows	1
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	4.0A
-------------------------------	------


Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-52213-001, AS-52213-001-JP
Packaging Specification	PK-52213-001
Product Specification	PS-52213-003, RPS-52213-001, RPS-52213-002, RPS-52266-001
Sales Drawing	SD-52213-002



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Compliant

Search Parts in this Series

52213 Series

Mates With

52266 Mizu-P25™ 2.50mm Pitch Waterproof Wire-to-Wire Plug Housing

Use With

50148 Mizu-P25™ Crimp Terminal

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Sealing Cap Hand Tool	0622024400
-----------------------	------------

Tool

Japan

Description

Product #

This document was generated on 08/19/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION