


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5051104091](#)
Status: **Active**
Overview: FFC-FPC (SMT)
Description: 0.50mm Pitch Easy-On™ Type FFC/FPC Connector, 1.90mm Height, Double Bottom Contact Type (FD19 Series), Right Angle, Surface Mount, ZIF, 40 Circuits

Documents:

| | |
|--|---|
| 3D Model | Product Specification 5051100001 (PDF) |
| Drawing (PDF) | Product Specification PS-505110-001 (PDF) |
| Product Specification 5051100000 (PDF) | RoHS Certificate of Compliance (PDF) |



Series image - Reference only

General

| | |
|----------------|--------------------|
| Product Family | FFC/FPC Connectors |
| Series | 505110 |
| Comments | Black Actuator |
| Overview | FFC-FPC (SMT) |
| Product Name | Easy-On™ |
| UPC | 887191626321 |

Physical

| | |
|--------------------------------|------------------------|
| Circuits (Loaded) | 40 |
| Circuits (maximum) | 40 |
| Color - Resin | Beige |
| Contact Position | Bottom |
| Durability (mating cycles max) | 10 |
| Entry Angle | 90° Angle |
| Mated Height | 1.90mm |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold over Nickel |
| Material - Plating Termination | Gold over Nickel |
| Material - Resin | Liquid Crystal Polymer |
| Net Weight | 324.100/mg |
| Number of Rows | 1 |
| Orientation | Right Angle |
| PCB Locator | No |
| PCB Retention | Yes |
| Packaging Type | Embossed Tape on Reel |
| Pitch - Mating Interface | 0.50mm |
| Pitch - Termination Interface | 0.50mm |
| Plating min - Mating | 0.051µm |
| Plating min - Termination | 0.051µm |
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -40°C to +105°C |
| Termination Interface: Style | Surface Mount |
| Wire/Cable Type | FFC/FPC |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 50V |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|---|
| Product Specification | 5051100000, 5051100001, PS-505110-001, RPS-505110-009 |
| Sales Drawing | SD-505110-001, SD-505110-002 |

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contains SVHC(2015 June 15): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[505110 Series](#)

This document was generated on 08/27/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION