

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008701039](#)
Status: **Active**
Overview: SPOX™ BMI Connector System
Description: 2.50mm Pitch SPOX™ Wire-to-Board Crimp Terminal, Reel

Documents:

[3D Model](#) [Product Specification PS-5264-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [5263](#)
 Application Signal
 Crimp Quality Equipment Yes
 Overview [SPOX™ BMI Connector System](#)
 Packaging Alternative [08-70-1040 \(Loose\)](#)
 Product Name SPOX™
 UPC 800753534902

Physical


Gender Female
 Material - Metal Phosphor Bronze
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 43.200/mg
 Packaging Type Reel
 Plating min - Mating 0.889µm
 Plating min - Termination 0.914µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.90mm max.
 Wire Size AWG 22, 24, 26, 28
 Wire Size mm² N/A

Material Info

Old Part Number 5263PBT

Reference - Drawing Numbers

Crimp Specification [CS-5263](#)
 Product Specification [PS-5264-001](#), [RPS-5263-001](#), [RPS-5264-002](#),
[RPS-5264-003](#), [RPS-5264-004](#), [RPS-5264-005](#),
[RPS-5264-006](#)
 Sales Drawing [SD-5263-003](#)



EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contains SVHC(2015
 June 15): No

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS
 ELV

Green Image
 Not Relevant

Search Parts in this Series

[5263](#) Series

Use With

[5264](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
FineAdjust™ Applicator for 2.50mm Pitch Crimp Terminal	0639023100
T2 Terminator for 2.50mm Pitch Crimp Terminal	0639123100

Hand Crimp Tool for 0638115200
Crimp Terminals
Manual Extraction 0638131400
Tool
FineAdjust™ 0639026400
Applicator for
2.50mm (.098")
Pitch SPOX™ Crimp
Terminal

Description	Product #
Applicator for M211A Bench Press, 22-28 AWG Wire	<u>0011260117</u>

This document was generated on 10/13/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION