

## Tilt Wall-Mount for 37" to 70" Flat-Screen Displays

MODEL NUMBER: **DWT3770X**



### Description

Tripp Lite's VESA-compliant DWT3770X Tilt Flat-Screen Wall Mount's low-profile design features an open frame for easy wall access and optimal display positioning flexibility. With tilt adjustment for improved viewing angles in applications where the audience is located below the display, it packs a lot of functionality into an unobtrusive frame. It can also free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 200 lbs. and fits most 37- to 70-inch flat-panel displays. It comes with all necessary mounting hardware and features horizontal adjustment to compensate for off-center wall studs. A built-in bubble level enables accurate display leveling. For peace of mind, the DWT3770X comes backed by a 5-year warranty.

### Highlights

- **REPLACES MODEL DWT3763X**
- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 37" to 70"
- Open frame for easy wall access
- Tilt adjustment improves viewing angles in applications where the audience is below the display
- Horizontal adjustment compensates for off-center wall studs
- Wide range of motion with -10° to 0° tilt capability
- Equipped with a bubble level for accurate display leveling
- Supports up to 200 lbs
- 5 year warranty

### Package Includes

- DWT3770X Tilt Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

## Specifications

PHYSICAL	
Mounting Location	Wall
Unit Weight (lbs.)	7.26
Unit Weight (kg)	3.29
Color	Black
Screen Size Compatibility (in.)	37 - 70
Screen Size Compatibility (cm)	93.98 - 177.80
VESA Pattern (mm)	100x100; 200x100; 200x200; 400x200; 400x400; 600x400; 800x400
Motion	Tilt
Degrees of Motion	-10/+0



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Distance from Wall (in.)	1.77
Distance from Wall (cm)	4.5
Maximum Weight Capacity (lbs.)	200
Maximum Weight Capacity (kg)	91
<b>FEATURES &amp; SPECIFICATIONS</b>	
Tools Necessary	Yes
Cord Management	No
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>