

Tilt Wall-Mount for 13" to 27" Flat-Screen Displays

MODEL NUMBER: DWT1327S



Description

Tripp Lite's VESA-compliant DWT1327S Tilt Flat-Screen Wall Mount's low-profile design stays hidden behind your display for a sleek, professional appearance. With tilt adjustment for improved viewing angles in applications where the audience is located below the display, it packs a lot of functionality into a compact frame. It can also free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 88 lbs. and fits most 13- to 27-inch flat-panel displays. It comes preassembled for quick and easy installation and features horizontal adjustment to compensate for off-center wall studs. For peace of mind, the DWT1327S comes backed by a 5-year warranty and green, RoHS-compliant design.

Highlights

- REPLACES MODEL DWT1323S
- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 13" to 27"
- Tilt adjustment improves viewing angles in applications where the audience is below the display
- Horizontal adjustment compensates for off-center wall studs
- Wide range of motion with -15° to +10° tilt capability
- Supports up to 88 lb
- 5-year warranty

Package Includes

- DWT1327S Tilt Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

Specifications

PHYSICAL	
Mounting Location	Wall
Unit Weight (lbs.)	1.01
Unit Weight (kg)	.45
Color	Black
Screen Size Compatibility (in.)	13 - 27
Screen Size Compatibility (cm)	33.02 - 68.58
VESA Pattern (mm)	75x75; 100x100
Motion	Tilt
Degrees of Motion	-15/+10 Tilt;
Min/Max Arm Extension (in.)	N/A



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Min/Max Arm Extension (cm)	N/A
Maximum Weight Capacity (lbs.)	88
Maximum Weight Capacity (kg)	39
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>