

Tilt Wall Mount for 60" to 100" Flat-Screen Displays

MODEL NUMBER: **DWT60100XX**



Highlights

- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 60 in. to 100 in.
- Supports up to 350 lbs.

Package Includes

- DWT60100XX Tilt Flat-Screen Wall Mount
- Mounting hardware
- Owner's manual

Description

Tripp Lite's VESA-compliant DWT60100XX Tilt Flat-Screen Wall Mount's low-profile design features an open frame for easy wall access and optimal flexibility for display positioning, allowing you to effortlessly reposition your display at any time, even after installation. It is ideal for freeing up valuable space in your workstation. The DWT60100XX packs a lot of functionality into an unobtrusive frame. It has a tilt adjustment with a wide range of motion (-15° to 15°) for improved viewing angles in applications where the audience is located below the display. Its durable, all-metal construction with scratch-resistant, powder-coat finish supports up to 350 lbs. and fits most 60" to 100" flat-screen displays. It comes with all the necessary mounting hardware. To help you install it perfectly, the DWT60100XX features a horizontal adjustment to compensate for off-center wall studs. For peace of mind, the DWT60100XX comes with a 5 year warranty.

Features

- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 60 in. to 100 in.
- Supports up to 350 lbs.
- Open frame for easy wall access
- Tilt adjustment improves viewing angles in applications where the audience is below the display
- Horizontal adjustment compensates for off-center wall studs
- Wide range of motion with -15° to 15° tilt capability

Specifications

PHYSICAL	
Mounting Location	Wall
Unit Dimensions (hwd / in.)	32.76 x 44.88 x 5.12
Unit Dimensions (hwd / cm)	83.2 x 113.0 x 113.0
Unit Weight (lbs.)	17.36



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.triplite.com

Unit Weight (kg)	7.36
Color	Black
Screen Size Compatibility (in.)	60 - 100
Screen Size Compatibility (cm)	152.4 - 254
VESA Pattern (mm)	200x200; 400x200; 300x300; 400x400; 800x400; 800x600; 1000x400; 1000x600; 1000x800
Motion	Tilt
Degrees of Motion	-15/+15
Maximum Weight Capacity (lbs.)	350
Maximum Weight Capacity (kg)	158.8
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.triplite.com/products/product-certification-agencies>