

4-Port Plug-n-Play USB 2.0 over Cat5/Cat6 Extender Hub, Transmitter and Receiver, Hi-Speed USB up to 164-ft. (50M)

MODEL NUMBER: **B203-104-PNP**



Description

Tripp Lite's High Speed Plug and Play USB 2.0 over Cat5 Extender Kit with 4-Port Hub allows placement of USB hub up to 50 meters (164ft) away from a source computer. Using solid conductor Cat5e rated cable, a full 480mbps transmission speed is maintained over the entire distance. Ideal for any situation where up to four USB devices need to be located more than the maximum 5-meter distance allowed by the USB timing signal. Also see B203-101-PNP for single device extension. For Solid Conductor patch cables, see Tripp Lite N202- series patch cables. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Kit includes Transmitter and 4port Hub Receiver
- Up to 50 meters (164ft) distance over Solid Conductor Cat5e/Cat6 cable
- Supports high speed data transfer rates up to 480mbps
- Plug and Play...no Drivers or Software required
- Backwards compatible to USB 1.1
- Windows and MAC compatible
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
Cable Type	USB; UTP (Cat5, Cat5e, Cat6, Cat6a)
PHYSICAL	

Highlights

- High Speed USB 2.0 over Cat5 4-port Hub Kit
- Up to 50 meters away from USB source
- Plug and Play...no Drivers or Software required
- Windows and MAC compatible
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Use with USB 2.0 peripherals that need to exceed the 16 ft. (5M) distance limitation

Package Includes

- Local transmitter unit
- Remote 4-port receiver unit
- External power supply (Input: 100-240V, 50/60Hz, 0.5A Output: 5V, 2A)
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	RJ45 (FEMALE) (X2)
Connector B	USB A (FEMALE) (X4)
Ports	4
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>